



Job Name:

Job Type:

Comments:

Quantity:

44362-965: Four-Light Rialto Wall / Bath Fixture

Dimensions:

Width: 30"

Extends: 8"

Height: 8 1/4"

Wire: 6 1/2"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box



Bulbs:

- 4 - medium A - Line 100w Max. 120v - Not included
- 4 - LED Medium LED A-19 8w 120v - Not included
- 4 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Arms - Steel - Antique Brushed Nickel

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Instruction Sheets:

English (HC-702)
French (F-007)

Collection: Rialto

Four Light Bath Bar in Antique Brushed Nickel Finish with Etched White Alabaster Glass Shades

Four-Light bath fixture in Antique Nickel finish and Etched White Alabaster glass.

UPC #:785652443619

Finish: Antique Brushed Nickel (965)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|------------------------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass | Etched White Alabaster | 1 | | | | | 6 | | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|------------|-----------------|-------|-------|----------|---------------|-----------------|
| Back Plate | 5 | 10 | 1/2 | | 5 3/4 | 2 1/2 |

Replacement Bulb Data:

| Product # | Type | Base | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S | A-19 | E-26 Medium | | | 120v | 50000 | 425 | 3000 | 85 |
| 97309S | A-19 | E-26 Medium | | | 120v | 50000 | 850 | 3000 | 85 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|-------|--------|----------|
| Individual | 44362-965 | 1 | 785652443619 | 32.6 | 11.6 | 9.6 | 2.101 | 10.55 | Yes |
| NJ Pallet | | 28 | | 48 | 40 | 72 | 80 | 295.4 | No |
| NV Pallet | | 28 | | 48 | 40 | 72 | 80 | 295.4 | No |