



Job Name:

Job Type:

Comments:

Quantity:

75360-965: Two-Light Rialto Close To Ceiling



Dimensions:

Diameter: 16"

Height: 14"

Height Flush: 13 1/4"

Height w/ Chain: 135 3/4"

Wire: 144" (color/Clear)

Chain: 120"

Mounting Proc.: Dual Mount

Connection: Mounted To Box

Bulbs:

- 2 - medium A - Line 100w Max. 120v - Not included
- 2 - LED Medium LED A-19 8w 120v - Not included
- 2 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture is dual mount and may be installed flush or as a pendant
- Supplied with 12' of Wire Pre-laced through 10' of Chain

Material List:

- 1 Body - Steel - Antique Brushed Nickel
- 1 Chain - Steel - Antique Brushed Nickel

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-960)
- French (F-003)

Collection: Rialto

Semi-Flush Convertible Fixture in Antique Brushed Nickel Finish with Etched White Alabaster Glass Shade

Two-light close-to-ceiling fixture in Antique Nickel finish with Etched White Alabaster glass.

UPC #:785652753626

Finish: Antique Brushed Nickel (965)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Etched White Alabaster	1					15				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1	5		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S			A-19	E-26 Medium			120v	50000	425	3000	85
97309S			A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	75360-965	1	785652753626	17.5	17.5	9	1.595	11.22	Yes
NJ Pallet		40		48	40	73	81.111	448	No
NV Pallet		40		48	40	73	81.111	448	No