

PFBFVM



# Foot Valve



## Product Features

- Bronze finish
- High capacity, 3" 175 WOG
- Soft seat for bubble tight shutoff, spring loaded for fast seating action
- Low cracking pressure, 1/2 PSI
- Flow profile designed to minimize head loss
- Perfect sealing both at high and low pressure
- Wide temperature range: +10° to 210° F
- High technology materials to ensure best resistance in any condition
- Patented obstructor guide
- Connection: female ANSI B 1.20.1
- Not for use at or below ground level
- Not for potable use



## Product Specification

PFBFVM



## Product Numbers

PFBFVM

	PART NAME	MATERIAL	QTY
1	Body	Brass CW 617N UNI EN 12165	1
2	End Connection	Brass CW 617N UNI EN 12165	1
3	Obstructor	Polyetherimide	1
4	Seat	NBR	1
5	Spring	Stainless Steel	1
6	Screen	Stainless Steel - Nylon	1

	SIZE	A	ØB	ØC	D	ØE	ØF	G	CH*	I	CV**	PSI	Lbs
PFBFVM	3"	4.86	3.84	5.24	4.82	3.70	4.03	9.68	3.86	1.01	158.00	175	6.15

\*CH is the nut size for the installer to use the correct wrench. \*\*CV is the number of gallons of water the valve will pass with a differential pressure of 1 PSI.

## Waranty and Codes

This PROFLO product carries a 1-year limited warranty



"Not for potable use"

Distributed Exclusively by Ferguson and Wolseley Canada