1015

CARSON® TrussT

COVER

Style: Flush
Material: HDPE
Model: 10" x 15"
Weight: 2 lbs

Std. Fasteners: 3/8" Hex Bolt

Options: Logos and Special Markings Surface: Skid Resistant & Marked

Performance: Pedestrian, ASTM C857, WUC 3.6

Cover comes standard with permanent markings for manufacturer and model size.

BODY

Material: HDPE
Model: 10" x 15"
Weight: 7" Depth: 4 lbs

12" Depth: 7 lbs

Wall Type: Flared Mouseholes: 0/2/6

Performance: Pedestrian, ASTM C857, WUC 3.6

C Ε F G Α В D 7" 16-1/2" 11-7/8" 19-1/4" 14-5/8" 17-1/2" 12-7/8" 12" 16-1/2" 11-7/8 20" 16" 18-5/8" 14"

 $10^{\frac{1}{4}}$ "

 $15\frac{3}{8}$

В


EXTENSION

Material: HDPE Weight: 4 lbs

LOAD RATING / NOTES



For use in non-vehicular traffic situations only. Weights and dimensions may vary slightly. Actual load rating is determined by the box and cover combination.



1015

CARSON® TrussT

COVER OPTIONS


HDPE, T-Cover Solid

HDPE, Flush Solid

HDPE, Flush with Plastic Reader Door

HDPE, Flush with Cast Iron Reader Door

HDPE, Flush Hinged



T-Cover Solid




Flush Solid

COLOR OPTIONS

Cover: Black, Green, Purple, Blue

Body: Black, Green, Purple

Extension: Black



Hinged Cover



Reader Door Detail

FASTENER OPTIONS

Snap-On (T-Cover)

ADD ON OPTIONS

Touch Read Hole EMS Marker





All information contained on this sheet is current at the time of publication. Oldcastle reserves the right to discontinue or update product information without notice.

Revision 11/30/18 © 2018 Oldcastle Infrastructure

