# PP975WM/BM

### GE Profile™ 36" Built-In CleanDesign Electric Cooktop


#### Dimensions and Installation Information (in inches)

KW Rating	
240V	8.9
208V	6.7
Breaker Size	
240V	40 Amps <sup>†</sup>
208V	40 Amps <sup>†</sup>

†Note: Check local codes for required breaker size Important: Requires a 5" free area between the bottom of the cooktop to any combustible material, i.e., shelving. Free area not required when installing wall oven underneath cooktop. Refer to installation instructions. Requires a 15" minimum from cooktop to adjacent overhead cabinets. Units are furnished with a 48" flexible armored cable.


Note: 36" Ribbon cooktops are approved for use over GE 30" Single Wall Ovens and Warming Drawers only. Refer to cooktop and wall oven/warming drawer installation instructions packed with product for current dimensional data. If installed with a GE Profile™ Telescopic Downdraft System, consult both the cooktop and downdraft installation instructions packed with product before installing. Cooktop gas/electric supply may need to be re-routed to install downdraft. The countertop must be at least 26" deep with a flat surface area of 23-1/2" or more, front to back. In addition, other clearances to the front edge of the countertop must be considered, especially on raised bullnose countertops. Consult cabinet and countertop manufacturer's specs for flush mount installation prior to install.

**Installation Information:** Before installing, consult installation instructions packed with product for current dimensional data.



\*Depth of unit at conduit connection location (rear) is 6-1/4" on models PP980/975/950/945 and 4-5/8" on models PHP960/900, PP972/962/942/932/912 and JP6SS/356/346/340.

\*\*Raised bull nose countertops may require up to 3/8" additional clearance to prevent interference with curved front.



For answers to your Monogram,® GE Profile™ or GE® appliance questions, visit our website at ge.com or call GE Answer Center® service, 800 626 2000.





## PP975WM/BM GE Profile™ 36" Built-In CleanDesign Electric Cooktop

#### **Features and Benefits**

- Electronic Touch Controls Offer easy, point-and-cook convenience
- Ribbon Heating Elements Provide powerful heat beneath a smooth glass surface to ensure even heat and fast warm-up times
- PowerBoil™ Element Provides up to 3,000 watts of power to speed the boiling process
- Dual Size Ribbon Element Offers a convenient choice of using a
  5" or 8" heating element depending on the size of the pan
- Control Lock Capability Provides the ability to lock controls, helping protect from unintentional activation
- Upfront Controls Controls are placed within easy reach at the front center of the cooktop
- Hot Surface Indicator Lights Illuminate when the cooking surface is active and hot, adding convenience and safe caution
- 12"/9"/6" Tri-Ring Element Accommodates various-sized pots or pans for the ultimate in cooking versatility
- Warming Zone Provides low heat capability for foods, making meal coordination simple
- Model PP975WMWW White on white
- Model PP975BMBB Black on black



