



Job Name:

Job Type:

Comments:

Quantity:

9485-15: Ambiance Accent Disk Light White



Dimensions:

Diameter: 3 1/8"

Wire: 72" (color/White)

Height: 7/8"

Bulbs:

1 - wedge T-5 18w Max. 12v - Not included

Features:

- Fixture is dual mount and may be installed flush or as a pendant

Material List:

- 1 Housing - Polycarbonate - White
- 1 Trim - Polycarbonate - White
- 1 Reflector - Anodized Aluminum - Satin Aluminum

Safety Listing:

- UL Listed for Wet Locations
- cUL Listed for Wet Locations
- cETL Listed

Instruction Sheets:

English (HC-207)

Ambiance Disk Lighting System Polycarbonate Housing with 36 Inch 18/2 Cord. Bulb Not Included.

Faceted polished aluminum reflector maximizes light output. Low profile polycarbonate disk lights can be surface mounted or recessed into as little as 3/4" thick material without boring through. Complete with 36" 18/2 cord. Surface mount ring and mounting screws included or a 2 3/4" diameter hole may be drilled in shelf fo recessed mounting.

Glass shield not required for UL listing.
Optional trims available for a variety of lighting effects.
For use with Class II transformer or select 9488 fused plug or Class I transformer.

Listed for Wet Location for 12V only; Recess dimension 7/32

UPC #:785652948510

Finish: White (15)

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
9774	Clear	Xenon	xenon T5	wedge	18	16.2	12v	10000	210	2800	
9775	Clear	Xenon			18	16.2	24v	10000	210	2800	
9776	Clear				8	8	12v	2500	57	2650	
9777	Clear				12	11.6	12v	2000	120	2750	
9778	Clear				18	16.2	12v	2000	210	2800	

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	9485-15	1	785652948510	7	6	1.5	0.036	0.2	Yes
Master Pack		5	10785652948517	5.78	5.78	5.78	0.112	1.1	Yes
Shipping Master		100	20785652948514	30.25	12.5	12.25	2.681	20	Yes

NJ Pallet		2000		48	40	65.2	72.444	479	No
NV Pallet		2000		48	40	65.2	72.444	479	No