
## **PFPCV Series**

## **PVC Spring Check Valves**



## **Product Features**

- . Solvent weld with EPDM seals and stainless steel spring
- Test pressure 225 psi, working pressure 100 psi
- · 2 psi minimum flow
- · Do not service or test compressed air or gas
- Not for use with hot water systems
- Max operating temperature 73°F





**PFPCVF** 

No.	Part Description	Material	Qty		
1	Upper Body	PVC	1		
2	Lower Body	PVC	1		
3	Spigot	PVC	1		
4	Connector Seat	PVC	1		
5	Spring	SS 304	1		
6	Seal	EPDM	1		

Product	Size		A		В		C		D		Е		F		G		Н	
	In	mm	In	mm	In	mm	In	mm	ln	mm	In	mm	In	mm	In	mm	In	mm
PFPCVF	3/4"	20mm	1.50"	38	1.38"	35	1.00"	25.3	0.99"	25.1	0.83"	21	2.21"	56	0.72"	18.26	4.13"	105
PFPCVG	1"	25mm	1.89"	48	1.77"	45	1.27"	32.3	1.27"	32.1	1.10"	28	2.87"	73	0.87"	22.22	5.24"	133
PFPCVH	1-1/4"	32mm	2.17"	55	2.05"	52	1.59"	40.3	1.59"	40.1	1.38"	35	3.58"	91	0.94"	23.82	6.18"	157
PFPCVJ	1-1/2"	40mm	2.48"	63	2.36"	60	1.98"	50.3	1.98"	50.1	1.54"	39	3.58"	91	1.01"	27.38	6.18"	157
PFPCVK	2"	50mm	2.99"	76	2.87"	73	2.49"	63.3	2.49"	63.1	2.05"	52	4.21"	107	1.16"	29.36	7.01"	178

## Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

