

SELECT® Residential Electric Water Heaters



Tall, Short and Lowboy models available.

Diffuser Dip Tube - Helps reduce lime and sediment buildup, maximizes hot water output. Made of State PEXAN™, a cross-link PEX polymer that can withstand long-term exposure to water temperatures up to 400°F.

Aluminum Anode Rod - Helps protect against corrosion for longer life.

Durable Tamper-Resistant Brass Drain Valve

Glass-Lined Tank - For long-lasting protection against rust and corrosion.

Upgrade Tank Warranty to 10 Years - See details on page 2.

Factory-Installed Side-Mounted Temperature & Pressure

(T&P) Relief Valve - Top-mounted T&P Valve available as option on some models.

6- Year Tank Warranty

6- Year Parts Warranty

Code Compliance - All models meet or exceed federal minimum energy standards effective January 20, 2004, according to latest editions of the National Appliance Energy Conservation Act (NAECA). They also comply with the latest editions of the BOCA National Codes, CEC, UBC, SBCC, CABO and the HUD standards. All models UL Listed according to safety specifications outlined in Underwriters Laboratories Inc. Standards for Safety (UL 174).



For more information on Select® contact:
State Water Heaters
500 Tennessee Waltz Parkway, Ashland City, TN 37015
800-365-0024 Toll-free USA
www.statewaterheaters.com


SRESS00706

February 2008R

SOLID.STATE.



©2008 State Industries



SELECT[®]

Residential Electric Water Heaters



MODEL NUMBER	PEAK DEMAND OUTPUT (1st Hour Rating Gallons)	ENERGY FACTOR	GALLON CAPACITY	ELEMENT WATTAGE 240 VAC		RECOVERY 90°F RISE	R VALUE	DIMENSIONS IN INCHES			APPROX. SHIPPING WEIGHT (LBS)
				STANDARD	MAXIMUM			A HEIGHT	B DIAMETER	C	
TALL MODELS											
ES6 30 DORT	43	.93	30	4500	6000	21	16	46-1/2	18	39-1/2	95
ES6 40 DORT	52	.92	40	4500	6000	21	16	59-1/2	18	53-1/2	115
ES6 52 DORT	60	.91	50	4500	6000	21	16	54	20-1/2	47-1/2	125
ES6 55 DORT	67	.90	55	4500	6000	21	16	60-1/4	20-1/2	52-3/4	135
ES6 66 DORT	72	.88	66	4500	6000	21	16	60-1/4	22	53	170
ES6 80 DORT	81	.86	80	4500	6000	21	16	60-1/2	24	52	200
ES6 120 DORT *	112	.81	119	4500	6000	21	16	64-1/4	28	54-1/4	320
SHORT MODELS											
ES6 30 DORS	43	.93	30	4500	6000	21	16	36-1/2	20-1/2	28	100
ES6 40 DORS	52	.92	40	4500	6000	21	16	44	20-1/2	37-3/4	115
ES6 50 DORS	62	.90	50	4500	6000	21	16	48	22	40-1/2	150
LOWBOY MODEL											
ES6 30 DOLS	41	.93	29	4500	6000	21	16	30	22	22-1/2	105
ES6 40 DOLNS	48	.92	38	4500	6000	21	12	31-1/4	23	24-5/8	125
ES6 50 DOLS	55	.91	50	4500	6000	21	16	34	26-1/2	25	170


Recoveries are rounded to nearest gallon

Water Connections - 3/4" on all models

For 10-Year Tank Warranty, change "6" to "X" in Model Number (ESX 40 DORT)

*This model is not available with top-mounted T&P Valve

10-Year Tank Warranty and top T&P Valve option combo not available on ES6 40 DOLNS and ES6 50 DOLS



*Location for optional top-mounted T&P Valve, if available and ordered from factory.

For complete information on limited warranties, consult written warranty, or contact the State Customer Care Center, 1-800-365-0024.

State Industries, Inc. reserves the right to make product changes or improvements without prior notice.

For more information on Select[®] contact:
 State Water Heaters
 500 Tennessee Waltz Parkway, Ashland City, TN 37015
 800-365-0024 Toll-free USA
 www.statewaterheaters.com

SOLID.STATE.

