

TAG:


Enclosed Epoxy Coated Hose Reel

Architect/Engineering Specifications:

Enclosed epoxy coated steel hose reel, high flow spray valve with swivel, 3/8" x 30' heavy-duty non-marking hose, ratcheting system, multi-fit bracket, adjustable hose bumper and 3/8" NPT female inlet.

6 1/2"

166mm



Features & Benefits:

- Enclosed epoxy coated steel hose reel
- Blue high flow spray valve w/ swivel
- 3/8" x 30' heavy-duty non-marking hose rated to 300 PSI
- Ratcheting system holds the length of hose until a slight tug to retract automatically
- 3/8" NPT female inlet
- Adjustable hose bumper
- Multi-fit bracket for wall, ceiling or under counter mounting
- Material: Epoxy coated steel open reel and wall bracket, polished chrome plated spray valve

Optional Hose Reel Spray Valves

□ B-0107	Med Flow Spray Valve
B-0108	Ergonomic Medium Flow Spray Valve
□ B-0108-H	Ergonomic High Flow Spray Valve
EB-0107	High Flow Spray Valve (Standard)
EB-2322	Extended Spray Wand
□ MV-2516-24	Stainless Steel Rear Trigger Water Gun
□ MV-2522-24	Stainless Steel Front Trigger Water Gun
□ MV-3516-24	Aluminum Rear Trigger Water Gun

Product Compliance:

- NSF 61 Exempt (Non-Potable)
- EPAct 2005 Non-Compliant (PRSV)

Warranty: Two Year (Limited)

Hose: One Year (Limited)

Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
- Flow Rate: 4.28 GPM @ 60 psi

Optional Hose Reel Multi-Fit Brackets

3/8" x 15', 30', & 35' Epoxy Coated Hose Reel

□ G016636-45	Epoxy Coated Wall Swing Bracket
□ G016652-45	Deck Mount Pivot Bracket
🗆 G018477-45	Stainless Steel Table Leg Swing Bracket



