


Type \_\_\_\_\_  
 -09 -10 -15 -109

P2779	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P2780	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P2781	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P2782	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>

**Finish**

**Dimensions (Inches)**

Catalog No.	Finish				Lamping	Dimensions (Inches)			
	Brushed Nickel	Polished Brass	Polished Chrome	Brushed Bronze		A	B	C	D
P2779	-09	-10	-15	-109	1 (m) 100w	5-3/4	9-1/2	7-1/2	6
P2780	-09	-10	-15	-109	2 (m) 100w	14	8-1/8	7-1/2	5-7/8
P2781	-09	-10	-15	-109	3 (m) 100w	22-3/8	8-1/8	7-1/2	5-7/8
P2782	-09	-10	-15	-109	4 (m) 100w	30-1/2	8-1/8	7-1/2	5-7/8



**Specifications:**

General

- Etched white opal glass shades, 5-3/4" dia. x 5-3/16" T, 1-11/16" center hole
- Brushed Nickel (-09), Polished Brass (-10), and Polished Chrome (-15) are plated finishes
- Brushed Bronze (-109) is a painted finish
- Can be mounted in the "up" or "down" position
- Steel construction

Mounting

- Wall mounted
- Oval shaped backplate, 7" W x 4-1/2" T x 1" deep
- Canopy covers a standard 4" hexagonal outlet box
- Mounting strap for outlet box included

Electrical

- Ceramic medium based sockets
- Pre-wired

Labeling

- UL-CUL damp location listed