


# Flared Copper Couplings

## Flare Copper to Flare Copper



### Flare Copper to Flare Copper (2 part) Coupling (supplied with wedding ring)

| CATALOG<br>NUMBER  | DESCRIPTION  |              | APPROX.<br>WT. LBS. |
|--------------------|--------------|--------------|---------------------|
|                    | FLARE COPPER | FLARE COPPER |                     |
| STRAIGHT COUPLINGS |              |              |                     |
| CS22-33-NL         | 3/4"         | 3/4"         | 0.6                 |
| CS22-44-NL         | 1"           | 1"           | 0.9                 |
| CS22-55-NL         | 1-1/4"       | 1-1/4"       | 0.9                 |
| CS22-66-NL         | 1-1/2"       | 1-1/2"       | 4.0                 |
| CS22-77-NL         | 2"           | 2"           | 6.7                 |

### Wedding Ring Only for (2 part) Coupling

| CATALOG<br>NUMBER    | SIZE AND COUPLING APPLICATIONS | APPROX.<br>WT. LBS. |
|----------------------|--------------------------------|---------------------|
| <b>WEDDING RINGS</b> |                                |                     |
| WR-3-NL              | 3/4" for CS22-33-NL            | 0.1                 |
| WR-4-NL              | 1" for CS22-44-NL              | 0.1                 |
| WR-5-NL              | 1-1/4" for CS22-55-NL          | 0.1                 |
| WR-6-NL              | 1-1/2" for CS22-66-NL          | 1.4                 |
| WR-7-NL              | 2" for CS22-77-NL              | 2.2                 |



### Flare Copper to Flare Copper (3 part) Coupling

| CATALOG<br>NUMBER  | DESCRIPTION  |              | APPROX.<br>WT. LBS. |
|--------------------|--------------|--------------|---------------------|
|                    | FLARE COPPER | FLARE COPPER |                     |
| STRAIGHT COUPLINGS |              |              |                     |
| C22-11-NL          | 1/2"         | 1/2"         | 0.6                 |
| C22-12-NL          | 1/2"         | 5/8"         | 0.7                 |
| C22-13-NL          | 1/2"         | 3/4"         | 0.8                 |
| C22-22-NL          | 5/8"         | 5/8"         | 0.8                 |
| C22-23-NL          | 5/8"         | 3/4"         | 1.0                 |
| C22-33-NL          | 3/4"         | 3/4"         | 1.0                 |
| C22-34-NL          | 3/4"         | 1"           | 1.3                 |
| C22-44-NL          | 1"           | 1"           | 1.9                 |
| C22-55-NL          | 1-1/4"       | 1-1/4"       | 2.7                 |
| C22-66-NL          | 1-1/2"       | 1-1/2"       | 4.5                 |
| C22-77-NL          | 2"           | 2"           | 8.4                 |
| ELL COUPLINGS      |              |              |                     |
| L22-33-NL          | 3/4"         | 3/4"         | 1.0                 |
| L22-34-NL          | 3/4"         | 1"           | 1.4                 |
| L22-44-NL          | 1"           | 1"           | 1.8                 |
| L22-66-NL          | 1-1/2"       | 1-1/2"       | 4.8                 |
| L22-77-NL          | 2"           | 2"           | 8.5                 |