



100 Royal Way
 Temple, GA 30179
 Phone (800) 520-6593

SPECIFICATION DATA SHEET

Date: 10/7/2009

MODEL No. 101
Snaplock Furnace Pipe

DIMENSIONAL DATA

SIZES AVAILABLE: 3" THROUGH 24" DIAMETER

FABRICATION DATA

Material:
 ASTM-A653 CS Type B Galvanized Steel,
 G-30 Coating LFQ Chemical Treatment

*G-90 Coating LFQ Chemical Treatment Available

<u>Diameter</u>	<u>Length Available</u>	<u>Gauges Available</u>
3"	2', 5'	30, 26
4"	2', 4', 5'	30, 26, 24
5"	2', 4', 5'	30, 26, 24
6"	2', 4', 5'	30, 26, 24
7"	2', 4', 5'	30, 26, 24
8"	2', 4', 5'	30, 26, 24
9"	2', 4', 5'	30, 26, 24
10"	2', 4', 5'	30, 26, 24
12"	2', 4', 5'	30, 26, 24
14"	2', 3', 4', 5'	28, 26, 24
16"	2', 3', 4'	28, 26, 24
18"	2', 3', 4'	26, 24
20"	2', 3', 4'	26, 24
22"	2', 3', 4'	26, 24
24"	2', 3', 4'	24

FEATURES

Male and Female Locks are roll formed using a Modified Reeves Design. Pipe has 3/8" stiffener beads Rolled every 12" for added rigidity.

OPTIONS

Aluminum in 4-14"-Fabricated from 3003-H14 in 26GA
 Stainless Steel 4-14"-Fabricated from T304 2B in 26GA
 Both Stainless and Aluminum are sold in 4' pieces.
 Matte Black available

