

Company name: Created by: Phone: Fax: Date: -

Date: -				
Position	Count	Description		Unit price
	-1	22 SQE05-40		On
			Product photo could vary from the actual product	request
		Product No.: 96160196		
		3" multi-stage, submersible pump designed for		
		domestic water supply, liquid transfer in tanks, irrigation and environmental applications. The		
		pump has "floating" impellers, each with its own		
		tungsten carbide/ceramic bearing.		
		The pump features soft starting and protection against dry-running, upthrust, overvoltage, undervoltage, overload and overtemperature.  The motor is a one-phase motor of the permanent magnet rotor type ensuring optimum efficiency within a wide load range.  The motor is fitted with a replaceable cable plug.		
		Liquid: Maximum liquid temperature: Max liquid temperature at 0.15 m/ Density:	95 °F /sec: 95 °F 62.4 lb/ft <sup>3</sup>	
		Technical:		
		Speed for pump data:	10700 rpm	
		Rated flow: Rated head:	22 US gpm 39.4 ft	
			UL, cUL CE,UL,CUL	
		Materials:		
		Pump:	Polyethylene / Stainless steel	
		Motor:	DIN WNr. 1.4301 Stainless steel DIN WNr. 1.4301 AISI 304	
		Installation:		
		Pump outlet:	NPT 1 1/2	
		Minimum borehole diameter:	2.99 in	



Company name: Created by: Phone: Fax: Date: -



Company name: Created by: Phone: Fax: -

Date:

## 96160196 22 SQE05-40 60 Hz

Printed from Grundfos CAPS [2012.01.058]

