


# Incandescent

# **Pavillion**

# **Bath & Vanity**

Type \_\_\_\_\_\_ -09 -20 P3294 □ □

_	Finish						
Catalog	Brushed	Antique		Dimensions (Inches)			
No.	Nickel	Bronze	Lamping	Α	В	C	D
P3294	-09	-20	3 (m) 100w	32-3/4	8-7/8	10-1/8	5-1/8



### **Specifications:**

#### General

- 8-3/4" dia. x 3-3/4" tall, 1-3/4" dia. center hole
- Etched watermark glass shades
- Concealed shade retainment
- Scroll arm with wound and twisted wire accents
- Can be mounted in "up" or "down" position
- Plated brushed nickel (-09) or antique bronze (-20) finishes
- Steel construction
- Companion fixtures: Hall and foyer, chandeliers, pendants, wall brackets, close to ceiling, and bath and vanity

### Mounting

- •Backplate is 12" W x 4-1/2" T x 1" deep
- Wall mount
- Back plate covers a standard recessed 4" octagonal outlet box
- Mounting strap for outlet box included Electrical
- Pre-wired
- Medium based ceramic sockets

### Labeling

• UL-CUL damp location listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607