



Job Name:

Job Type:

Comments:

Quantity:

88242-780: Single Light Wall Lantern



Dimensions:

Width: 11"

Extends: 13 3/4"

Height: 26 1/4"

Wire: 6 1/2"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box

Bulbs:

- 1 - medium A - Line 100w Max. 120v - Not included
- 1 - LED Medium LED A-19 8w 120v - Not included
- 1 - LED Medium LED A-19 13.5w 120v - Not included

Material List:

1 Body - Aluminum - Burled Iron

Safety Listing:

UL Listed for Wet Locations
cUL Listed for Wet Locations / Non-IC

Instruction Sheets:

English (HC-1180)
French (F-006)

Collection: Cape May

One Light Wall Lantern in Burled Iron Finish with Etched Hammered with Light Amber Glass Shade

UPC #:785652242786

Finish: Burled Iron (780)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Etched Hammered with Light Amber	1				10 15/32	8 5/8				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	18 1/8	4 1/2	1		9 1/8	17 7/16

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	88242-780	1	785652242786	15.75	13.5	27	3.322	11.6	Yes
NJ Pallet		21		48	40	72.5	80.556	243.6	No
NV Pallet		21		48	40	72.5	80.556	243.6	No