



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
7.00"	29.50"	8.50"
<u>BP Height</u>	<u>BP Width</u>	
4.76"	6.50"	
<u>Hanging Weight</u>		
9.65 lb		

Lamping:

Incandescent MB	4,600 Rated Lumens
4.00 60W MB	Color Temperature
240 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
12.98 lb	11.00"	9.25"	29.00"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209054301	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Steel

Certification:

Damp Location
Location

Additional:

MB (Not Included)
Lighting Direction: Both