TOTO®

MS864114E/MS863113E

Eco Supreme® One-Piece Toilet, 1.28GPF

FEATURES

- E-Max[®] flushing system, low consumption (1.28GPF/4.8LPF)
- One-piece decorative toilet with low-profile tank
- Elongated front bowl with SoftClose[®] seat (SS114) or round front bowl with SoftClose[®] seat (SS113)
- 12" Rough-in
- Chrome trip lever

MODELS

- MS864114E Elongated bowl with SoftClose seat (SS114)
- MS863113E Round bowl with SoftClose seat (SS113)

COLORS/FINISHES

Standard
#01 Cotton
#03 Bone
#11 Colonial White
#12 Sedona Beige

PRODUCT SPECIFICATION

The one-piece low consumption E-Max flushing system toilet shall be 1.28GPF/4.8LPF. Toilet shall be of elongated front bowl (MS864) or round front bowl (MS863) with a low-profile tank and SoftClose seat. Toilet shall have chrome trip lever. Toilet shall be TOTO Model MS864114E_____ (elongated), MS863113E_____ (round).





CODES/STANDARDS

- Meets and exceeds ASME A112.19.2/CSA B45.1
- Certifications: IAPMO(cUPC), EPA Watersense, State of Massachusetts, City of Los Angeles, and others
- Code compliance: UPC, IPC, NSPC, NPC Canada, and others
- Legislative compliance: California AB715, California Green Building Code, City of Los Angeles Water Efficiency Ordinance



MS864114E/MS863113E

Eco Supreme® One-Piece Toilet, 1.28GPF

SPECIFICATIONS

- Water Use 1.28 GPF/4.8LPF
- Flush System


E-Max[®]


- Min. Water Pressure 8 psi (static)
- Water Surface 10-1/4" x 8-1/4" 2-1/8"
- Trap Diameter .
- Rough-in
- 12"
- Trap Seal 2-1/4"
- Warranty One Year Limited Warranty
- Material Vitreous china
- Shipping Weight MS864114E 89 lbs. MS863113E 85 lbs.
- Shipping Dimensions 29-1/2" L x 18"W x 19-1/4" H1 x 27-1/8" H2

INSTALLATION NOTES

Back-to-Back Toilet Installations:

TOTO recommends the use of a nationally listed, double sanitary tee-wye only, in vertical waste stacks, in accordance with the stipulations noted in the majority of nationally recognized plumbing codes.





TOTO

These dimensions and specifications are subject to change without notice