

PEXRITE® THE TORCHLESS INSTALLATION[™]

PEX Stub-Out

Pick Your Stub-Out Method


Patents Issued or Pending

PEX to Copper

Stub-Out



(800) 321-0316 • www.holdrite.com



ADDITIONAL APPLICATION SOLUTIONS

PEXRITE[®] #705

3/8" & 1/2" CTS PEX tubing
Sink/Lavatory & Toilet stub-out
Overhead 90° turn
In-slab turn-out from decking into wall

PEXRITE[®] #706

3/8" & 1/2" CTS PEX tubing
Ideal for radiant heating application
Multi-run versatilty for manifolds

PEXRITE[®] #707

Up to 7/8" O.D. PEX tubing, soft copper, and flexible conduit
In-slab installation at groundwork with rebar or wood decking
Multi-run versatilty for manifolds

PEXRITE[®] #708

- Double run Pop-up with side entry
- Up to 1-1/8" O.D. PEX tubing, soft copper, and flexible conduit
 In-slab installation at groundwork with rebar or wood decking
 Multi-run versatilty for manifolds

PEXRITE[®] #708-E

Double run Pop-up
Up to 2-1/2" IPS rigid conduit 90s, flexible conduit (smirf tubing), PEX, and soft copper
Mounts directly to decking or with rebar for slab-on-grade installation





















PEXRITE POP-UP INSTALLATION INSTRUCTIONS





PIPE SUPPORT BRACKETS AND STUB-OUT SUPPORTS ····					
MODEL # DESCRIPTION					BOX QTY
103-18	Galvar	Galvanized bracket with 1-3/8" keyed holes, 20" long.			50
103-26	Galvar	alvanized bracket with 1-3/8" keyed holes, 26" long.			50
709	Galvanized bracket with 1-3/8" keyed holes, 7-1/5" long.			50	
709-L	Galvanized "L" bracket with 1-3/8" keyed holes.			50	
709-EXT	Galvanized bracket with 1-3/8" keyed holes and up to 8" center line off floor.				50
721	Galvanized bracket 3.38" x 2.25" with keyed hole. Integrates with the HOLDRITE STOUT BRACKET® or mounts directly to stud.				50
110-R	Galvanized bracket for lavatory/sink.				50
SB1S		Galvanized telescoping bracket, 10" - 18", supports PEX, Copper and CPVC.			
SB2S		nized telescoping bracket, 13" - 25", supports PE	50		
PEXRITE [®] PEX STUB-OUTS ···· • • • • • ···					
MODEL #	DESCRIPTION BOX QTY				
704	Turn-out supports 3/8" & 1/2" CTS PEX tubing. No tools required. Temp. range: -10° F to +180° F				100
705	Turn-out supports 3/8" & 1/2" CTS PEX tubing. Mount to block of wood. Sink/ lavatory & toilet stub-out support & overhead 90° turns. Temp. range: -10° F to				50
PEXRIT	TE® PEX TO COPPER STUB-OUTS ····				
MODEL #	DESCRIPTION BOX QTY				
701	Stub-out clamp supports 1/2" CTS PEX, Copper & CPVC tubing. No tools required. Temperature range: -10° F to +140° F				50
701-0536P	Stub-out clamp supports 1/2" CTS PEX tubing & 1/2" CTS 3.5" x 6" Copper Ell.			25	
701-0538P	Stub-out clamp supports 1/2" CTS PEX tubing & 1/2" CTS 3.5" x 8" Copper Ell.				25
103-18-701	20" flat, galvanized bracket & 1/2" CTS #701 stub out clamps.				50 brackets/ 100 clamps
103-26-701	26" flat, galvanized bracket & 1/2" CTS #701 stub out clamps.				50 brackets/ 100 clamps
PEXRI1	RITE® 6 PAKs ····				
MODEL #	DESCRIPTION KIT QTY 6PAK QTY				
704-PR	PEX stub-out Kit for Sink/Lavatory & Toilet applications. (1) #103-18 and (2) #704 Turn outs. (List Price: 6PAK=\$32.88, CASE=\$197.28)				
701-PR		PEX to Copper stub-out Kit. (1) #103-18, (2) #701 Clamps, & (2) 1/2" CTS 3.5" x 8" Copper Ells. (List Price: 6PAK=\$88.14, CASE=\$528.84)			
PEX POP-UP™ SUPPORTS ····●●●•···					
MODEL # DESCRIPTION BOX QTY					
706	Single run 3/8" & 1/2" CTS Pop-up for PEX. Ideal for in-slab and radiant heating. Temp. range: -10° F to +190° F. 50				
707	Single run Pon-up for PEX soft conner and flexible conduit. Tube sizes up to				25
708	Double	Double run Pop-up for PEX, soft copper and flexible conduit. Tube sizes up to 1-1/8" O.D. Temp. range: -10° F to +190° F.			
708-E	Double run Pop-up for PEX, flexible conduit (smirf tubing),& rigid conduit 90s. Tube sizes up to 2-1/2" IPS. Temp. range: -10° F to +190° F.				15
MODEL		DESCRIPTION	BAG QTY	MAST	ER CASE QTY
161, 162, 1		Thru-stud isolator for 1/2", 3/4" and 1" tubing.	50/50/25	500/500/250	
181, 182, 183		Single-nail clamp for 1/2", 3/4" and 1" tubing.	100/50/25	-	00/500/250
404-R, 405-R, 406-R		1/2", 3/4" and 1" CTS Fire Retardant inserts. Meets UL94 V-2.	100/30/23	N/A	
		(800) 321-0316 • wvvww.ho	drite com		