



Pro 24" Deep Wall Ventilation Hoods

With standard features like heat sentry and dual setting halogen lighting, Wolf pro wall hoods provide the ultimate in ventilation. Pro 24" deep wall hoods are available in seven widths.



Model PW482418 shown.

FEATURES

- Stainless steel finish.
- Heavy-duty, 16-gauge brushed stainless steel with continually welded seams, hemmed edges and sides.
- Stainless steel enclosed liner.
- Recessed easy-access controls.
- Infinite-speed blower control.
- Heat sentry feature automatically turns unit on when heat is sensed and automatically adjusts blower speed.
- Halogen lighting with two settings.
- Removable, dishwasher-safe, restaurant-grade stainless steel baffle filters.
- Transition with backdraft damper included.

MODEL OPTIONS

Model	PW302418	PW362418	PW422418	PW482418	PW542418	PW602418	PW662418
Overall Width	30"	36"	42"	48"	54"	60"	66"

BLOWER OPTIONS

CFM	INTERNAL				IN-LINE		REMOTE			
	500	600	900	1200	600	1100	600	900	1200	1500
PW302418		•	•		•	•	•	•	•	•
PW362418 PW422418		•	•			•		•	•	•
PW482418 PW542418				•	•	•		•	•	•
PW602418 PW662418				•		•			•	•

ACCESSORIES

- Internal, in-line and remote blowers (refer to chart above).
- 38" high stainless steel backsplash with or without warming racks.
- 6", 12", 18", 24" and 30" stainless steel duct covers.
- Horizontal discharge kit.
- Recirculating kit (30" and 36" wide hoods).



Model PW422418 Pro Wall Hood

Accessories are available through your authorized Wolf dealer. For local dealer information, visit the find a showroom section of our website, wolfappliance.com.



Recessed controls.




Baffle filters.



Pro 24" Deep Wall Ventilation Hoods

OVERALL DIMENSIONS




Unit dimensions may vary by $\pm 1/8$ ".

SPECIFICATIONS

Exterior Finish	Stainless Steel
Overall Widths	30", 36", 42", 48", 54", 60" and 66"
Overall Height	18"
Overall Depth	24"
Bottom of Hood to Countertop	30" to 36"
Discharge	Vertical or Horizontal*
Duct Size	10" Round
Electrical Requirements	110/120 V AC 60 Hz, 15 amp dedicated circuit
Shipping Weight	67–126 lbs

*Horizontal discharge applications require a horizontal discharge kit.

INSTALLATION SPECIFICATIONS



INSTALLATION NOTES

Pro 24" deep wall hoods are sold as a shell only. An internal, in-line or remote blower is required. For blower recommendations, visit our website, wolfappliance.com.

Pro 24" deep wall ventilation hoods are recommended for use with all Wolf cooking appliances.

IMPORTANT NOTE: For optimal performance, a pro 27" deep wall hood is recommended for use with ranges and rangetops that contain a charbroiler or griddle.

Complete installation specifications can be found on our website, wolfappliance.com.

Dimensions in parentheses are in millimeters unless otherwise specified.