



D510544T

D510544T

## SPECIFICATIONS

### SIRIUS™ SHOWER ONLY TRIM SINGLE HANDLE PRESSURE BALANCE FAUCET


#### Model

D510544T (Shower only trim)  
D510544LST (Shower only trim, less showerhead)  
D510444T (Valve only trim)

#### Description

- 5" X 8" showerhead D460060
- 2.5gpm (9.5L/min) maximum flow rate @ 80 psi
- 15" brass showerarm
- Metal lever handle
- Use with valve: D1120 series (w/ stops) or D1150 series (w/o stops) or D1125 series (w/ stops) or D1155 series (w/o stops)

#### Flow Rate



D510544T (shown)

#### Standards



- UPC/Cupc
- Energy Policy Act of 1992

MEETS ASME  
A112.18.1M/ A112.18.1

- ASME A112.18.1M/ A112.18.1




- ADA Accessibility Guidelines for Buildings and Facilities - 4.27.4 Controls and Mechanisms

#### Warranty

Danze products are covered by a manufacturer's limited "lifetime" warranty for manufacturing defects.

#### Finishes Available

- Chrome
- Other: Refer to Price List for additional finish



#### Submittal Information:

Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Contractor: \_\_\_\_\_

Contact #: \_\_\_\_\_