

The Zonix™

FP4620 Series




SPECIFICATION SHEET



Product Specifications Subject To Change

ZONIX™

FP4620** / FP4630SN Ceiling Fan



	A	B
Fan w/6" downrod	15.40"	12.90"
Fan w/12" downrod	21.40"	18.90"
Fan w/18" downrod	27.40"	24.90"
Fan w/24" downrod	33.40"	30.90"
Fan w/36" downrod	45.40"	42.90"
Fan w/48" downrod	57.40"	54.90"
Fan w/60" downrod	69.40"	66.90"
Fan w/72" downrod	81.40"	78.90"

INSTALLATION REQUIREMENTS:

Fan must be attached to a securely anchored electrical junction box capable of withstanding a load of at least 50 lbs.

ELECTRICAL REQUIREMENTS:

Requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

MOTOR SPECS:

153 x 18 motor is designed for optimal performance with this fan. 220 VAC, 50 Hz export version available.

BLADES:

A set of three 26" reversible cherry/walnut wood blades is included.

Optional sets of three 20" wood blades are available in reversible cherry/walnut (B4442CWR) and satin nickel (B4442SN) finishes—sold separately. Optional sets of three 20" composite blades are available in cherry (BPW4442CY) and walnut (BPW4442WA) finishes—sold separately.

CONTROL OPTIONS:

CW40 fan-only wall control is included. Reversing switch located on fan housing. Instructions are provided with each control. Optional C2 wall control and C4 hand-held remote with receiver are available—sold separately.

LIGHTING OPTION:

A single-bulb downlight fixture with 13 watt, energy-efficient CFL bulb included is available—sold separately. Maximum downlight wattage not to exceed 13 watts. *NOTE: Fan supplied with fan only wall control. Light kit will require use of C25* wall control and/or C4FL hand-held remote control with receiver unit—sold separately.*

*C25 wall control must be used with C4 remote control

DOWNROD OPTIONS:

Fan comes with a 1" dia. x 6" long downrod (DR1-6). Optional downrods available in 12", 18", 24", 36", 48", 60" and 72" lengths. A downrod coupler is available for installations requiring a downrod longer than 72". Fan can be mounted on a sloped ceiling up to 30°. Most sloped ceiling installations require a downrod longer than the standard 6" downrod. Optional sloped ceiling ball kits (SCB1-52) are available for slope angles greater than 30° and up to 52°. Call technical support for more information.

LOCATION USE:

Fan is rated for dry locations only, however, is damp location rated if used with composite blades listed above.

Available Finishes

OB	Oil-rubbed bronze—reversible cherry/walnut
SN	Satin nickel—reversible cherry/walnut
SN	Satin nickel—satin nickel

Airflow / Energy Efficiency Info (120V)

Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	145	4529	83	0.45	55
H-Med	99	2987	108	0.32	28
L-Med	70	2008	133	0.23	15
Low	49	992	126	0.17	8



celebrating 25 years

**10983 Bennett Parkway
Zionsville, IN 46077**

Toll Free (888) 567-2055

FAX (866) 482-5215

Outside U.S. call (317) 733-4113

Visit Our Website @ www.fanimation.com

*Copyright 2010 Fanimation, Inc.
All Rights Reserved*



2010/01