


The Windpointe®

BLADE SELECTION SERIES FANS

MA7300 / MA7400 / MA7500




SPECIFICATION SHEET





Product Specifications subject to change

WINDPOINTE® SERIES

Fan Motor Assembly

MA7300 Series	
Fan Motor Assembly (188 x 25)	Available Finishes
	MA7300MW – Matte White (Damp)
	MA7300OB – Oil-Rubbed Bronze
	MA7300RS – Rust* (Damp)

MA7400 Series	
Fan Motor Assembly (188 x 25)	Available Finishes
	MA7400AB – Antique Brass*
	MA7400OB – Oil-Rubbed Bronze
	MA7400PW – Pewter

MA7500 Series	
Fan Motor Assembly (188 x 25)	Available Finishes
	MA7500AB – Antique Brass*
	MA7500MW – Matte White (Damp)
	MA7500OB – Oil-Rubbed Bronze
	MA7500PW – Pewter
	MA7500RS – Rust* (Damp)

*220 VAC, 50 Hz export version available in this finish.

MA7300 Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	112	5301	99	0.45	54
Med	93	4171	111	0.38	38
Low	57	2514	152	0.25	17

Blade sweep varies depending on blade selection, see chart on page 79

MA7400 Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	170	5129	104	0.42	49
Med	131	3867	124	0.34	31
Low	79	2257	165	0.22	14

Blade sweep varies depending on blade selection, see chart on page 79

MA7500 Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	110	3468	82	0.37	42
Med	97	3010	88	0.33	34
Low	63	1743	106	0.23	17

Blade sweep varies depending on blade selection, see chart on page 79

INSTALLATION REQUIREMENTS:

Fan must be attached to a securely anchored electrical junction box capable of withstanding a load of at least 50 lbs.

ELECTRICAL REQUIREMENTS:

Requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

FAN SPEEDS / BLADES:

3 fan speeds with pull chain and reversing switch (on switch cup housing). Speeds will vary depending on blade size and type. All blade sets are sold separately. See our catalog or visit www.fanimation.com for available blade options.

CONTROL OPTIONS:

Optional C1, C2 and C25* wall controls and C4 remote control with receiver unit are available—sold separately. Instructions are provided with each control.

*C25 wall control must be used with C4 remote control

LIGHTING OPTIONS:


Optional lighting fitters and light kits are available. See our catalog or visit www.fanimation.com for lighting options.

DOWNROD OPTIONS:

Fan comes with a 1" dia. x 6" long downrod (DR1-6). Optional downrods are available in 12", 18", 24", 36", 48", 60" and 72" lengths. Fan can be mounted on a sloped ceiling up to 30°. Most sloped ceiling installations require a downrod longer than the standard 6" downrod. Optional sloped ceiling ball kits (SCB1-52) are available for up to 52°. Call technical support for more information.

BLADE SWEEP INFORMATION

Blade-Selection Fans



The following fans have varying blade sweeps from 44" to 80" depending on blade selection:

- The Americana®
- The Belleria®
- The Bourbon Street®
- The Islander®
- Louvre®
- Sandella®
- The Torrento®
- Treventi®
- The Windpointe® - 3-blade fans
- The Windpointe® - 4-blade fans
- The Windpointe® - 5-blade fans

Use the charts below to determine blade sweep.

5-Blade Fans		
Blade	Blade Length	Blade Sweep
<i>Palm Leaf (Dry Location Only)</i>		
ISP2, ISP5	18"	44"
ISP1, ISP4, ISP1RB, ISP4RB	22"	52"
<i>Woven Bamboo (Dry and Damp Locations Only)</i>		
ISD2A	18"	44"
ISD1A, ISD4A, ISD7A, ISD1C, ISD4C, ISD7C	22"	52"
<i>Wood (Dry Location Only)</i>		
B6030CY, B6030MH, B6030MP, B6030TK	30"	68"
B6000CY, B6000MH, B6000MP, B6000TK	36"	80"
<i>All-Weather Composite (Dry, Damp and Wet Location)</i>		
BPD5A	18"	44"
BPW20CY, BPW20MH, BPW20TK	20"	48"
BPW10CY	20.5"	49"
BPD1A, BPD4A, BPD4BL, BPD4MW, BPP1, BPP4, BPP1BR, BPD4BR, BPP4GR	22"	52"

4-Blade Fans		
Blade	Blade Length	Blade Sweep
<i>Wood (Dry Location Only)</i>		
B4010CP, B4020SS, B4040CP	22"	52"
B4000CA	26"	60"
B4060CP	36"	80"

3-Blade Fans		
Blade	Blade Length	Blade Sweep
<i>Wood (Dry Location Only)</i>		
B2040BL, B2070CP, B3000BW, B3000IM	24"	56"
<i>Bamboo and Wicker (Dry and Damp Locations Only)</i>		
B4000CA	26"	60"



celebrating 25 years

**10983 Bennett Parkway
Zionsville, IN 46077**

Toll Free (888) 567-2055

FAX (866) 482-5215

Outside U.S. call (317) 733-4113

Visit Our Website @ www.fanimation.com

*Copyright 2010 Fanimation, Inc.
All Rights Reserved*



2010/01