


SUBMITTAL INFORMATION

Uni-Flange Restraint (UFR1390-C-x-X-I style)



UNI-FLANGE SERIES 1390-C RESTRAINT DEVICE FOR C900 PVC PIPE BELL JOINTS CAST SIZES 4" - 12", WITH 304 STAINLESS STEEL HARDWARE





Nom Pipe Size	PVC PIPE WITH DI PIPE OD STYLE 1390-C		A	B Approx	C Max	RESTRAINING RODS		CLAMPING BOLTS		DC May	BC Min	✓ SUBMITTED
						No. Size		No.	SIZE BC MAX	BC IVIAX	BC WIIN	ITEMS
	OD	CATALOG NO.				D	E	F	G			
4"	4.80	UFR1390-C-4-X-I	1-1/8"	9-1/8"	15"	2	3/4" x 17"	4	5/8" x 3-1/2"	7.50"	7.14"	
6"	6.90	UFR1390-C-6-X-I	1-1/8"	11-1/8"	15"	2	3/4" x 17"	4	5/8" x 3-1/2"	9.50"	9.14"	
8"	9.05	UFR1390-C-8-X-I	1-1/4"	14-5/8"	15"	2	3/4" x 17"	4	3/4" x 4"	12.98"	11.36"	
10"	11.10	UFR1390-C-10-X-I	1-3/8"	16-5/8"	22"	4	3/4" x 24"	4	7/8" x 5"	15.00"	13.50"	
12"	13.20	UFR1390-C-12-X-I	1-3/8"	19-1/4"	22"	4	3/4" x 24"	4	7/8" x 5"	17.62"	15.62"	

FEATURES

- 4" 12" sizes: Cast ductile iron per ASTM A536 grade 65-45-12
- 360° contact and support of the pipe wall
- Restraining rods, clamping bolts and hardware are 304 stainless steel
- Rated at full-rated pressure of any class of PVC pipe, minimum 2:1 safety factor
- Also for use on ductile iron pipe with the following pressure ratings: 4" through 8" = 250 psi
 10" and 12" = 200 psi
- Black e-coat epoxy-coated

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443 Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167 www.fordmeterbox.com

07/15/15

Submitted By: