


PFCB20DFG

Copper Bonded Steel Bracket




Product Features

- 16 gauge copper bonded steel
- Holes on 2" (50.8mm) centers to position 1/2" (12.7mm) copper tubing and holes on 4" (101.6mm) centers to position 3/4" (17.7mm) and 1" (25.4mm) copper tubing




PFCB20DFG

No.	Description	Box Qty.
PFCB20DFG	20" (508mm) length	50



PFCB20DFG

Product Specifications



Installation Instructions

- Solder copper tubing to the bracket. Heat the pipe, not the bracket.
- Load rating 25 lbs.

