



THE MAX SERIES High Output “M” Coils



THE ALLSTYLE ...MAX...

U.S. PATENT
5,284,027

**MAXIMUM COOLING CAPACITY
MAXIMUM SEER RATING
MAXIMUM AIR FLOW**


MINIMUM HEIGHT

**Better air flow, BTUs, & SEER in a
shorter, more compact package!**

AllStyle Coil Co., L.P.



THE MAX SERIES High Output "M" Coils



Specify coil width needed when ordering.

Example: AS24-M140* +D-5 LH

Specify left or right hand refrigerant and drain connections.

Example: AS24-M140*+D -5 LH

3/4" MPT primary & secondary drain connections are standard

3/8" liquid line connection

Suction line connections
1.5 to 3.0 ton 3/4"
3.5 to 5.0 ton 7/8"

Standard Coil Cabinet Heights

CABINET DIMENSIONS									
Cabinet Model Number	Uncased Coil Depth	Uncased Coil Width	Cabinet Width "F"	Cabinet Depth "S"	Leaving Air Width "L"	Leaving Air Depth "P"	Entering Air Width "W"	Entering Air Depth "D"	Cabinet Height
5S	21.00"	13.00"	13.50"	21.50"	11.75"	19.75"	12.25"	20.25"	***
5	21.00"	13.00"	14.50"	21.50"	12.75"	19.75"	13.00"	20.25"	***
5G	21.00"	13.00"	14.00"	21.50"	12.25"	19.75"	12.75"	20.25"	***
6	21.00"	15.00"	16.50"	21.50"	14.75"	19.75"	15.25"	20.25"	***
6S	21.00"	17.00"	17.25"	21.50"	15.50"	19.75"	16.00"	20.25"	***
6A	21.00"	17.00"	18.00"	21.50"	16.25"	19.75"	16.75"	20.25"	***
6H	21.00"	15.00"	15.50"	21.50"	13.75"	19.75"	14.50"	20.25"	***
6G	21.00"	17.00"	17.50"	21.50"	15.75"	19.75"	16.25"	20.25"	***
6R	21.00"	17.00"	17.50"	21.50"	15.75"	19.75"	16.25"	20.25"	***
7	21.00"	17.00"	18.50"	21.50"	16.75"	19.75"	17.25"	20.25"	***
7H	21.00"	17.00"	19.13"	21.50"	17.38"	19.75"	18.13"	20.25"	***
8S	21.00"	20.00"	20.50"	21.50"	18.75"	19.75"	19.25"	20.25"	***
8	21.00"	21.00"	21.25"	21.50"	19.50"	19.75"	20.25"	20.25"	***
8A	21.00"	24.00"	24.50"	21.50"	22.75"	19.75"	13.50"	20.25"	***
8G	21.00"	21.00"	21.00"	21.50"	19.25"	19.75"	20.00"	20.25"	***
8H	21.00"	21.00"	22.75"	21.50"	21.00"	19.75"	21.75"	20.25"	***
8Y	21.00"	21.00"	22.25"	21.50"	20.50"	19.75"	20.00"	20.25"	***
9	21.00"	24.00"	25.50"	21.50"	23.75"	19.75"	24.25"	20.25"	***
9G	21.00"	24.00"	24.50"	21.50"	22.75"	19.75"	23.50"	20.25"	***

*** Cabinet Height will vary depending on the coil used
Specifications subject to change without notice

Coil	Cabinet Height
ASXX-M224G	16.25"
ASXX-M226G	16.25"
ASXX-M244G	18.25"
ASXX-M246G	18.25"
ASXX-M264G	20.25"
ASXX-M266G	20.25"
ASXX-M284G	23.25"
ASXX-M286G	23.25"
ASXX-M204G	25.00"
ASXX-M206G	25.00"
ASXX-M2Y4/6G	26.25"
ASXX-M2Z4/6G	28.25"
ASXX-M2S4/6G	30.25"

AllStyle Coil Co., L.P.