



512 nVent CADDY EZ Riser for Close Quarters – 5120200EG



- Innovative design eliminates loose hardware, simplifying installation
- Serrated flange-head bolts eliminate need for wrenches on both bolt and nut
- Short ears allow for use in spaces where full-sized risers do not fit
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)



| | |
|-----------------------------|-------------------|
| Part Number | 5120200EG |
| Material | Steel |
| Finish | Electrogalvanized |
| Pipe Size | 2" |
| Outer Diameter (OD) | 2 3/8" |
| Hole Size (HS) | 7/16" |
| A | 6 5/8" |
| B | 1 3/16" |
| Static Load (F) | 255 lb |
| Certifications | cULus |
| Standard Packaging Quantity | 25 pc |
| UPC | 78285661605 |

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

