


PRODUCT RANGE - FITTINGS


aquatherm ELBOW 90° (MOLDED, BUTT-FUSION)

The length of some fittings may not accommodate all butt-fusion equipment. Verify the equipment to be used is compatible with the fittings when ordering.



SDR	Part No.	Dimension (ND — OD)	d	z	Weight
			[in]	[in]	[lb]
7.4	0112130	6" — 160 mm	6.30	5.71	5.65
9	0312130	6" — 160 mm	6.30	5.71	5.23
	0312134	8" — 200 mm	7.87	8.23	10.9
	0312138	10" — 250 mm	9.84	9.45	19.8
11	0112131	6" — 160 mm	6.90	5.71	5.65
	8112135	8" — 200 mm	7.87	8.23	9.26
	8112139	10" — 250 mm	9.84	9.45	16.9
17.6	8412130	6" — 160 mm	6.30	5.71	3.62
	8412134	8" — 200 mm	7.87	8.23	6.45
	8412138	10" — 250 mm	9.84	9.45	11.8

aquatherm ELBOW 45° (MOLDED, SOCKET)



Part no.	Dimension (ND — OD)	d	z	l	D	Weight
		[in]	[in]	[in]	[in]	[lb]
0112508	½" — 20 mm	0.79	0.20	0.77	1.16	0.03
0112510	¾" — 25 mm	0.98	0.24	0.87	1.34	0.04
0112512	1" — 32 mm	1.26	0.30	1.00	1.69	0.08
0112514	1 ¼" — 40 mm	1.57	0.37	1.18	2.05	0.12
0112516	1 ½" — 50 mm	1.97	0.45	1.38	2.68	0.25
0112518	2" — 63 mm	2.48	0.55	1.63	3.31	0.50
0112520	2 ½" — 75 mm	2.95	0.65	1.83	3.94	0.77
0112522	3" — 90 mm	3.54	0.77	2.07	4.72	1.25
0112524	3 ½" — 110 mm	4.33	0.93	2.38	5.79	2.26
0112526	4" — 125 mm	4.92	1.06	2.64	6.57	2.93