


aquatherm greenpipe® - transition piece with male thread

with hex shaped threaded transition

Material : **fusiolen®** PP-R, brass
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	l	z	D	R	SW	Weight
	Nom. I.D.	pc	[in]	[in]	[in]	[in]	[in]		lb/pc
0121306	3/8" X 1/2" M	10	0.63	2.62	2.11	1.52	1/2"	0.87	0.27
0121308	1/2" X 1/2" M	10	0.79	2.62	2.05	1.52	1/2"	0.87	0.26
0121310	1/2" X 3/4" M	10	0.79	2.66	2.09	1.52	3/4"	0.94	0.28
0121312	3/4" X 3/4" M	10	0.98	2.66	2.03	1.52	3/4"	0.94	0.28
0121314	1" X 1" M	5	1.26	3.09	2.38	2.09	1"	1.26	0.54
0121316	1" X 1.25" M	5	1.26	3.19	2.48	2.68	1 1/4"	1.61	0.79
0121317	1.25" X 1" M	5	1.57	3.19	2.38	2.05	1"	1.26	0.55
0121318	1.25" X 1.25" M	5	1.57	3.33	2.52	2.68	1 1/4"	1.61	0.80
0121319	1.5" x 1.25" M	5	1.97	3.37	2.44	2.68	1 1/4"	1.61	0.86
0121320	1.5" X 1.5" M	5	1.97	3.48	2.56	2.91	1 1/2"	1.81	1.06
0121321	2" X 1.5" M	1	2.48	3.90	2.81	2.85	1 1/2"	1.81	1.15
0121322	2" x 2" M	1	2.48	4.04	2.95	3.31	2"	1.97	1.56
0121323	2.5" X 2" M	1	2.95	4.09	2.91	3.31	2"	1.97	1.66
0121324	2.5" X 2.5" M	1	2.95	4.13	2.95	3.94	2 1/2"	2.56	2.26
0121325	3" X 3" M	1	3.54	4.96	3.66	4.72	3"	3.35	3.37
0121327	3.5" X 4" M	1	4.33	5.83	4.37	5.79	4"	4.13	6.21