


aquatherm greenpipe® - flange adapter

with gasket

Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green




Art.- No.	Dimension	PU	d	l	z	D	D1	l1	z1	Weight
	Nom. I.D.	pc	[in]	[in]	[in]	[in]	[in]	[in]		lb/pc
0115512	1"	1	1.26	1.38	0.67	1.61	2.68	0.43	0.12	0.07
0115514	1.25"	1	1.57	1.44	0.65	1.97	3.07	0.49	0.12	0.10
0115516	1.5"	1	1.97	1.56	0.63	2.40	3.46	0.47	0.12	0.14
0115518	2"	1	2.48	1.71	0.63	2.99	4.02	0.61	0.12	0.22
0115520	2.5"	1	2.95	1.81	0.63	3.54	4.80	0.63	0.12	0.32
0115522	3"	1	3.54	1.97	0.67	4.25	5.43	0.67	0.12	0.56
0115524	3.5"	1	4.33	2.19	0.73	5.16	6.22	0.73	0.12	0.72
0115526	4"	1	4.92	2.48	0.91	5.91	7.08	0.79	0.12	1.04
0115527	4"	1	4.92	2.48	0.91	5.91	7.08	0.79	0.12	1.04

aquatherm greenpipe® - flange adapter

with gasket

Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	z	d1	D	l	l1	z1	Weight
	Nom. I.D.	St	[in]	[in]	[in]	[in]	[in]	[in]	[in]	lb/pc
0115530	6" -- SDR 7.4	1	6.30	3.66	8.35	6.89	0.98	0.86	2.09	2.56
0115531	6" -- SDR 11	1	6.30	3.66	8.35	6.89	0.98	0.57	2.09	2.10
0115534	8" -- SDR 7.4	1	7.87	5.12	10.55	9.13	1.26	1.08	2.83	4.41
0115535	8" -- SDR 11	1	7.87	5.12	10.55	9.13	1.26	0.72	2.83	4.41
0115538	10" -- SDR 7.4	1	9.84	5.12	12.60	11.22	1.38	1.35	2.95	4.41
0115539	10" -- SDR 11	1	9.84	5.12	12.60	11.22	1.38	0.89	2.95	4.41