## ADJUSTABLE FLOOR DRAIN WITH DECK FLANGE

Halo Drain™ 822 series

**SPECIFICATION** 

Sioux Chief 822 series adjustable floor drain shall be used where necessary in drainage systems. Floor drain shall allow adjustment of 3/4" above the deck flange. Floor drain shall have a Sch. 40 hub connection. Deck Flange shall be 18 gauge stainless steel and attach to deck with screws or nails. Strainer shall be heel-proof and meet all applicable load requirements for intended use. Trap primer port shall be threaded ½" FIP for knockout connection. Designed in accordance with ASME A112.6.3-2001

#### **MATERIALS**

ring/strainer: nickel-bronze, 304 stainless steel, 18 GA. stainless steel

head adapter / coring sleeve: ABS coring plug: high-impact polymer deck flange: 18 GA. 430 stainless steel

base adapter: ABS, PVC

#### STRAINER LOAD RATING

nickel-bronze: 1,000 lbs. (light duty, pedestrian traffic) 304 stainless steel: 2,000 lbs. (light duty, pedestrian traffic) 18 GA. stainless steel: 500 lbs. (light duty, pedestrian traffic)

#### STRAINER FREE AREA

round: 7.5 in2 (22.75 gpm)\* square: 12.75 in<sup>2</sup> (39 gpm)\* 18 GA.: 5.75 in<sup>2</sup> (17.5 gpm)\*

#### **DIMENSIONS**

2" × 3" or 3" × 4" Sch. 40 hub A: connection size\*\*

B: ring/strainer diameter

51/2" / 57/8" round / square C: flange diameter 91/2" D: body diameter 51/8" E: body height 43/8"

F: adjustable finish height\*\*\*

0"-3/4" / 5/16"-3/4" / 0"-1/2"round / square / 18 GA.

G: trap primer port 1/2" FIP thread for knockout connection

\* Indicates flow rate of the strainer (not necessarily of the fixture) at 1/2" head.

### Create Item Number

# 822-ABCD

e.g. 822-3PSQ = Finish Line Halo drain with 3" PVC hub connection, and 304 square stainless steel ring and strainer

<u>A</u>	CLAMPING COLLAR	<u>B</u>	CONNECTION	<u>C</u>	RING & STRAINER
(skip if no collar is necessary)		□ 2A	2" ABS Sch. 40 hub	□ NR	round cast nickel-bronze
□ M	Clamping collar kit included	□ 2P	2" PVC Sch. 40 hub	□ NQ	square cast nickel-bronze
(No collar is standard unless otherwise specified)		□ 3A	3" ABS Sch. 40 hub	□ SR	round cast stainless steel
		□ 3P	3" PVC Sch. 40 hub	□ SQ	square cast stainless steel
				□S	18 Gauge stainless steel <sup>1</sup>


D Options **ACCESSORIES** 

□ 822-EX3 Extension nipple<sup>3</sup> □ 863-FA 4" aluminum funnel  $\Box$  V Vandal-resistant strainer screws

Complies with Buy American Act<sup>2</sup> □ 863-FN 4" nickel-bronze funnel □ 832-S3 shim kit

2 Available only on round nickel-bronze ring & strainer □ 822-TB Thread bushing

3 Extends head 1-3/4" (min) to 3-3/8" (max) above deck flange







1 Drain head creates plastic rim around strainer

<sup>\*\*</sup> Adapters fit over 2"/inside 3" pipe, or over 3"/inside 4" pipe.

<sup>\*\*\*</sup> When using clamping collar, min dimension is ½".