


CO-200-R

Tag: _____

Floor Cleanout with Round Top

SPECIFICATION: Watts Drainage CO-200-R epoxy coated cast iron floor cleanout with 5" (127) round adjustable gasketed nickel bronze top, removable gas tight gasketed brass cleanout plug, and no hub (standard) outlet.



Components R 34B

Pipe Sizing (Select One)		
Suffix	Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	

	Outlet Type (Select One)	
Suffix	Description	
NH	No Hub (M)	
P	Push On	
Х	Inside Caulk	

Options (Select One or More)		
Suffix	Description	
-C	Membrane Clamp	
-6	Vandal Proof	
-13	Galvanized Body	
-CF	Carpet Cleaning Flange	
-US	Buy American Compliant	

Optional Body Material		
Suffix	Description	
-60	PVC Body w/Poly Plug	
-61	ABS Body w/Poly Plug	

Chart A

	NH(MJ)	Р	60/61
Pipe	No	Push	PVC/
Size	Hub	On	ABS
2"	4-1/2" (114)	5-1/2" (140)	4" (102)
3"	4-1/2" (114)	5-1/2" (140)	4" (102)
4"	4-3/4" (121)	5-1/2" (140)	4" (102)



* The load classifications are in accordance with the American National Standards ASME A112.21.1M ASME Ratings are as follows: MD - Safe Live Load 2000-4999 lbs.(900-2250kg)

MD - Safe Live Load 2000-4999 lbs. (900-2250kg The above categories are given as a guide only. Please consult factory.

Job Name	Contractor
Job Location	Contractor's P.O. No.
Engineer	Representative

WATTS Drainage reserves the right to modify or change product design or construction without prior notice and without incurring any obligation to make similar changes and modifications to products previously or subsequently sold. See your WATTS Drainage representative for any clarification. Dimensions are subject to manufacturing tolerances.



Specification Drainage Products

USA: 100 Watts Road, Spindale, NC, 28160-2298; TEL: 828-288-2179 TOLL-FREE: 1-800-338-2581 www.watts.com

ES-WD-CO-200-R USA 1304 CO-200-R