
SUBMITTAL INFORMATION

Straight Single Check Valve - (HS11-xxx-NL style)



FEMALE IRON PIPE INLET BY FEMALE IRON PIPE OUTLET Access Cap EPDM Rubber O-Ring Brass Valve Body Polypropylene **Plastic Valve Stem EPDM Rubber Seal** Stainless Steel Spring Female Iron Pipe Female Iron Pipe Inlet Outlet Length

VALVE SIZE	Inlet Size	OUTLET SIZE	Length	Approx. Wt. Lbs	Part Number	✓ Submitted Item(s)
3/4"	3/4"	3/4"	3-3/8"	1.2	HS11-333-NL	
1"	1"	1"	3-9/16"	1.4	HS11-444-NL	

FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (ASTM B584, UNS C89833)
- The product has the letters "NL" cast into the main body for lead-free identification
- Certified to NSF/ANSI Standard 61 and NSF/ANSI Standard 372 where applicable
- · Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS C83600, 85-5-5-5)
- In-line accessible for guick inspection and replacement of internal working parts without removing the valve from the service line. Replacement kits are available.
- Poppet assembly includes polypropylene plastic poppet, 302 stainless steel spring and EPDM rubber seal
- 175 PSI maximum working water pressure
- 180 degree Fahrenheit maximum constant temperature

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.

	The Ford Meter
FORD	P.O. Box 443, Wabas
FUND	Phone: 260-563-3171
	Overseas Fax: 260-5
	www.fordmeterbox.co

Box Company, Inc. h, Indiana U.S.A. 46992-0443 / Fax: 800-826-3487 63-0167 bm 04/02/15 Submitted By: