

Item #: P4086-1-084	UPC Code:
Product Family Name:	Finish: Brushed Nickel
Category: Low Voltage Track	Category Type: LightRail
Certification	
Patents	
Notes:	



Image File Name:
P4086-1-084.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
	120	11	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
8		No	8.29
Canopy Width:	Canopy Height:	Canopy Length:	
5.75	5.25		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:



LAMPING

No. of Bulbs:	Light Type:			
6	Mr-16 (Gu5.3,12v)			
Max Bulb Wattage:	Socket:			
35	Gy6/Gu5/3g4,2-Pin			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
No				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHADE / GLASS

Description:		Material:
White Acid Etched		Glass
Part No.:		Quantity:
		6
Width:	Height:	Length:
3.25	2.25	



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
6.000	10.000	41.250	
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:	
11.770	1.430	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1