TOTO®

CST424EF(G)

EcoPromenade Closed Coupled Toilet, 1.28 GPF




CST424EF - EcoPromenade Closed Coupled Toilet with SS114 - SoftClose Seat



Quiet, powerful, commercial grade flushing performance.



toilet seat, or upgrade to a Washlet.



E-Max® Technology: Choose a SoftClose® Fast Flush: New, wide 3" flush valve is 125% larger than conventional 2" flush valves.



TOTO USA, Inc. recommends the use of a nationally listed, double sanitary tee-wye only, in vertical waste stacks, in accordance with the stipulations noted in the majority of nationally recognized plumbing codes.

- Traditional design with stately lines
- Powerful and quiet flush
- Promenade design suite: Matching pedestal and self-rimming lavatories
- Large water surface
- Universal Height

High profile, elongated, close coupled toilet. Low consumption (1.28 Gpf/4.8 Lpf) gravity flushing action.

Tank cover, fittings, chrome plated trip lever less seat.

CST424EF

Elongated, 12" rough-in, less seat.

■ CST424EFG

Elongated, 12" rough-in, less seat. SanaGloss glazing. (Available in: #01)

☐ C424EF

Elongated front bowl only, 12" rough-in.

☐ C424EFG

Elongated front bowl only, 12" rough-in. SanaGloss glazing. (Available in: #01)

☐ ST424E

Promenade tank and cover only. Complete with tank trim and coupling components.

☐ SS114

SoftClose: Seat and lid gently close with a touch of a hand. Elongated, closed front seat with lid.

ADA Compliant

(For installation condition with approach from left hand side)

Colors:

Standard #01 Cotton, #11 Colonial White #12 Sedona Beige, #03 Bone

#51 Ebony

Trip Lever:

Standard #CP Chrome Plated Optional See price book for additional finishes

CST424EF(G)

Eco Promenade Close Coupled Toilet, 1.28 GPF

■ PERFORMANCE

The TOTO® E-Max® low consumption toilets received high ratings during ANSI/ASME and CSA testing at independent laboratories. Designed with a powerful siphon jet flushing action, the toilet offers a large water surface and a glazed trapway. Promenade toilets are designed to match the Promenade Lavatory Suite.

■ SPECIFICATIONS

Water Use:

1.28 Gpf / 4.8 Lpf

Flush System:

Gravity Feed

Min. Water Pressure: 8 psi

Water Surface:

8-7/8" x 6-3/8"

Trap Diameter:

2-1/8"

Rough-in:

12" rough in

Trap Seal:

2-1/4"

Material:

Vitreous china

Warranty:

One Year Limited Warranty

Shipping Weight:

C424EF(G) - Bowl 59 lbs.

ST424E - Tank 41.5 lbs.

Shipping Dimensions:

C424EF(G) - Bowl

28"L x 10"W1 x 16-1/4"W2 x 17-1/4"H

ST424E - Tank

20-1/2"L x 9-1/2"W x 21-3/4"H

Fixture dimensions and hydraulic performance meet or exceed ANSI/ASME standard A112.19.2 and CAN/CSA B 45 requirements.

Listing and approval: IAPMO/UPC, CSA, City of Los Angeles, State of MA, and others


WaterSense compliant.

Meets and exceeds ASME A112.19.2 standards for drainline carry distance with a 2% grade and 4" I.D. pipe.



Meets the American Disabilities Act Guidelines and ANSI A117.1. For installation condition with approach from left hand side.

These dimensions and specifications are subject to change without notice.



CST424EF(G) - Eco Promenade Close Coupled Toilet



TOTO U.S.A., INC. • 1155 Southern Road, Morrow, GA 30260 Tel. (888) 295-8134 • Fax. (800) 699-4889 • www.totousa.com Printed in U.S.A. © TOTO LTD. 03/08 #SS-00237 V.03