Below Deckmount Sink Faucets 8" Centers





SPECIFICATION: (EXAMPLE)

- · Below deckmount sink faucet
- 203mm (8") centers, two handle
- · Polished chrome-plated finish trim
- CAST BRASS bodies
- BRASS swing spout or 3/8" IPS BRASS PIPE Rigid/Swivel Gooseneck Spout
- Metal hold-down package
- Color indexed metal handles with vandal resistant screws
- CER-TECK® 1/4 turn ceramic structures

and... with... (add spout required) with... (add outlet required) with... (add handle required)

> with... (add suffix -LS if required – see back page) with... (add suffix -TI if required - see back page)

27C2144



Engineer/Architect Approval

Model Specified:

Approval: Date:

MODEL NUMBER EXAMPLE:

Configurations vary, see below for availability.

27C2944-LS

Variation

1 = 8" (203 mm) Wallform spout 2 = 8" (203 mm) Tubular spout

9 = 6" (152 mm) Gooseneck spout

Outlet

2 = Vandal resistant laminar outlet 1.5 gpm (5.7 L/min) 3 = Vandal resistant aerator 1.5 gpm (5.7 L/min) 4 = Standard aerator outlet 1.5 gpm (5.7 L/min)

5 = Vandal resistant spray outlet

0.5 gpm (1.9 L/min) 7 = Smooth end, laminar outlet 1.0 gpm (3.8 L/min)

Handle

2 = Hooded blade

3 = Hooded lever

4 = Blade w/sanitary hood 5 = Wrist w/sanitary hood

"H" (red), "C" (blue) R*= Optional gooseneck

spout dimensions: R2 = 4.5" long, 11.9" high

LS = 120° Limited swing gooseneck

TI = Handle temperature indicators

R5 = 6" long, 13.4" high

dimensions:

AVAILABLE MODELS

Hooded Blade

4" (102 mm)



Wallform S2 Spout 8" (203 mm)

27C2122

27C2142

27C2123

27C2124

27C2144



27C2222

27C2232

27C2242

27C2233

2702243

27C2243-TI

27C2232-S7





27C2922

27C2922-LS

27C2922-R7

27C2932-R7

27C2932

27C2923







27C2943-LS-R7

27C2943-LS-TI

27C2943-R5

27C2943-R7

27C2943-TI

27C2934

27C2934-LS

27C2934-R2

27C2934-R5

27C2934-R7

27C2944-LS

27C2944-R7

27C2944-LS-TI

27C2944



2



Blade with

Sanitary Hood

4" (102 mm)

5

Wrist with


6" (152 mm)











27C2253 27C2224 27C2234 27C2244


27C2245

2702933 27C2933-LS 27C2933-R7 27C2943 27C2924 27C2924-LS 27C2924-LS-R6 27C2924-LS-R7TI

27C2924-LS-TI 27C2924-R2TI

27C2924-R5 27C2924-R7 27C2924-TI

27C2935 27C2945-R7 27C2955 27C2975



27C2953 27C2953-LS-TI

27C2973

27C2954

27C2974

27C2954-R6

27C2954-R7

27C2974-R5

27C2974-R7

27C2974-TI

27C2974-R5TI

27C2953-R7

Note: Use this page front and back as a product submittal sheet.

Flow Rates are at 60 PSI. Refer to www.specselect.com for individual models.

Below Deckmount Sink Faucets 8" Centers






APPROVALS:

- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- Indicates compliance to ICC/ANSI A117.1
- Verified compliant with 0.25% weighted average Pb content regulations

(Contact Delta Representative for State and/or Local Approvals.)

FLOW RATE vs PRESSURE





HANDLE TEMPERATURE INDICATORS

☐ Suffix "-TI" signifies handle temperature indicators "H" (red), "C" (blue). Available on selected models.



LIMITED SWING GOOSENECK


☐ Suffix "- LS" signifies 120° Limited Swing. Available on selected models.

FOR OPTIONAL RIGID/SWIVEL & LIMITED SWING SPOUTS

See **DSP-R/S** for detailed specification.

FOR OPTIONAL SWING SPOUTS

See **DSP-S/S** for detailed specification.



GOOSENECK SPOUT ASSEMBLIES								
SPOUT/OUTLET	"A"		"C"		"L"			
SPUUI/UUILEI	mm	in.	mm	in.	mm	in.		
Gooseneck–Standard (R4) for outlets #2, 3, 4 & 5	152	6	124	4.9	146	5.8		
Gooseneck-Standard (R4) for outlet #7	152	6	117	4.6	152	6.0		

44mm (1.75")

SWING SPOUT ASSEMBLIES										
SPOUT	SPOUT/OUTLET	"A"		"C"		"L"				
NO.	3F001/001LE1	mm	in.	mm	in.	mm	in.			
1	8" Wallform Spout (S2)	206	8.1	15	0.6	130	5.1			
2	8" Tubular Spout (S5)	185	7.3	41	1.6	147	5.8			

Note: Measurements may vary ± 6mm (0.25")

Refer to www.specselect.com for individual models.

Note: Use this page front and back as a product submittal sheet.

4

5

in.

0.69

0.69

0.67

0.69

17

18

44mm (1.75")