

l ledical and	Lavatory	Faucet
----------------------	----------	--------

B-0831-02VR


Slow Self-Closing Metering Faucet

TAG:

Architect/Engineering Specifications:

4" centerset deck mount mxing faucet with polished chrome plated brass body and integral spout, VR 0.5 GPM non-aerated spray device, metering cartridges, push button caps and 1/2" NPSM male inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372. Meets ADA ANSI/ICC A117.1 requirements.

Job Name	
Model Specified	Quantity
Variations Specified_	
Date	





Features & Benefits:

- 4" centerset deck mount mixing faucet w/ polished chrome plated brass body and integral spout
- VR 0.5 GPM non-aerated spray device, Series 8 (B-0199-08-N05)
- Metering cartridges
- Adjustable metering cycle, 10 to 30 seconds
- Push button (hot & cold) caps w/ vandal resistant screws
- 1/2" NPSM male inlets
- · Material: Polished chrome plated brass body & spout and chrome plated metal caps

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)

Warranty: One Year (Limited)

Performance Data:

Pressure: 20 - 125 psi Temperature: 40°F - 140°F

Flow Rate: 0.50 GPM @ 60 psi

Water Consumption: @ 10 sec = .08 gal, @ 15 sec = .13 gal



Optional Outlets (Series 3 / VR Series 8)

GPM	Aerated	Non-Aerated (Laminar)	VR Aerated	VR Non-Aerated (VR Laminar)	Optional Cartridges
0.35	N/A	□ B-0199-03-N035	N/A	□ B-0199-08-N035	□ Push Button Metering (Standard)
0.5	N/A	□ B-0199-03-N05	N/A	Standard	□ Pivot Action Metering
1.0	N/A	N/A	N/A	□ B-0199-08-LF-10	□ Wrist Action Metering
1.5	□ B-0199-03-WS	N/A	□ B-0199-08-WS	N/A	
2.2	□ B-0199-03	□ B-0199-26	□ B-0199-08	□ B-0199-28	







T&S BRASS AND BRONZE WORKS, INC.

