



Pipe Diameter	Outside Dia. O.D.	Flange Thickness T	Inside Dia. I.D.	Bolt Count N	Dia. Bolt Hole B.D.	Bolt Circle B.C.	Radius r	Weight lbs/pc	Operating Pressure	FERGUSON PART #
1/2"	3.5	0.5	0.9	4	0.63	2.38	0.13	1	335	
3/4"	3.88	0.5	1.11	4	0.63	2.75	0.13	1	335	IBUPSDR70075C
1"	4.25	0.56	1.38	4	0.63	3.13	0.13	1	335	IBUPSDR701C
1 1/4"	4.63	0.63	1.72	4	0.63	3.5	0.19	2	335	IBUPSDR70125C
1 1/2"	5	0.69	1.97	4	0.63	3.88	0.25	2	335	IBUPSDR70150C
2"	6	0.75	2.46	4	0.75	4.75	0.31	3	335	IBUPSDR702C
2"	6	0.5	2.63	4	0.75	4.75	0.2	1.5	200	IBUPSDR1102B
2 1/2"	7	0.88	2.97	4	0.75	5.5	0.31	4	335	IBUPSDR70250C
3"	7.5	0.94	3.6	4	0.75	6	0.4	4	335	IBUPSDR703C
3"	7.5	0.53	3.75	4	0.75	6	0.28	2.5	200	IBUPSDR1103B
4"	9	0.94	4.6	8	0.75	7.5	0.4	5.5	335	IBUPSDR704C
4"	9	0.55	4.75	8	0.75	7.5	0.28	3.5	200	IBUPSDR1104B
5"	10	0.94	5.69	8	0.88	8.5	0.44	6	335	IBUPSDR705C
6"	11	1	6.75	8	0.88	9.5	0.4	7	335	IBUPSDR706C
6"	11	0.63	6.88	8	0.88	9.5	0.28	4.5	200	IBUPSDR1106B
8"	13.5	1.12	8.75	8	0.88	11.75	0.4	11	335	IBUPSDR708C
8"	13.5	0.85	8.88	8	0.88	11.75	0.28	8	200	IBUPSDR1108B
10"	16	1.19	10.92	12	1	14.25	0.4	16	335	IBUPSDR710C
10"	16	0.98	11	12	1	14.25	0.31	12	200	IBUPSDR1110B
12"	19	1.5	12.92	12	1	17	0.4	23	335	IBUPSDR712C
12"	19	1.25	13.13	12	1	17	0.28	20	200	IBUPSDR1112B
14"	21	1.63	14.18	12	1.13	18.75	0.4	37	335	IBUPSDR714C
14"	21	1.38	14.38	12	1.13	18.75	0.31	30	200	IBUPSDR1114B
16"	23.5	1.88	16.19	16	1.13	21.25	0.4	49	335	IBUPSDR716C
16"	23.5	1.65	16.38	16	1.13	21.25	0.35	40	200	IBUPSDR1116B
18"	25	1.9	18.2	16	1.25	22.75	0.4	50	335	



Pipe Diameter	Outside Dia. O.D.	Flange Thickness T	Inside Dia. I.D.	Bolt Count N	Dia. Bolt Hole B.D.	Bolt Circle B.C.	Radius r	Weight lbs/pc	Operating Pressure	FERGUSON PART #
18"	25	1.67	18.38	16	1.25	22.75	0.35	45	200	IBUPSDR1118B
20"	27.5	2.13	20.38	20	1.25	25	0.31	61	335	
20"	27.5	1.81	20.38	20	1.25	25	0.4	55	200	IBUPSDR1120B
22"	29.5	2.3	22.38	20	1.38	27.25	0.31	79	335	
22"	29.5	2	22.38	20	1.38	27.25	0.37	65	200	IBUPSDR1122B
24"	32	2.13	24.38	20	1.38	29.5	0.31	91	250	IBUPSDR924B
24"	32	2.17	24.38	20	1.38	29.5	0.4	73	200	IBUPSDR1124B
30"	38.75	2.28	30.38	28	1.38	36	0.31	113	125	IBUPSDR1730B
36"	46	2.75	36.38	32	1.63	42.75	0.31	170	125	IBUPSDR1736B

1. Operating pressure on an HDPE flange adapter with a safety factor of 2.