STEAMIST®

Steam Generator

Models: TSG-7 and TSG-10

Features

Limited lifetime warranty - 2-year in home labor warranty where available

Generator typically can be installed up to 25 ft. from the bathing area

Selectable "Instamist"

Steady Steam™

"Gangable" up to (4) generator

Diagnostic LED Displays


Stainless Steel Construction

Solid-State Circuitry

Codes/Standards

UL 499

UL/CUL Listed



Steam Generator Specification Chart						
Model Number	Product Number	KW Rating	* Max. Cu. Ft. Range	Volts/Phase/ Max. Amps	Line Fuse	Dimensions L x W x H
TSG-7	7520 7521 7522 7523	7.5	250	240/1/31 208/1/36 240/3/18 208/3/21	40 50 30 30	15" x 6" x 15.5"
TSG-10	1020 1021 1022 1023	10	450	240/1/42 208/1/48 240/3/24 208/3/28	50 60 30 40	15" x 6" x 15.5"

Refer to sizing guidelines to accurately determine the proper size generator for the installation.

90°C copper wire is required for generator connection. Installation shall be in accordance with NEC and local electrical codes.

Required Equipment

TSC Model Control

Required Electrical Service

Dedicated circuit required: See Specification Chart for proper electrical requirements

Product Information

Water Supply - %" Compression Fitting, 120 PSI Max

Steam Line - 3/4" Brass BPT male thread

Pressure Relief Valve - 3/4" NPT female thread

Drain Line - Capped 1/2" Brass NPT male thread

Generator

Weight - 30 lbs.

Installation Notes

Steam Generators can be typically mounted within 25 ft. of the bathing area.

Steam Generators should be accessible for service.


Do not install in attic.

Do not install generators outside, in a moist, humid area or in an area where parts may freeze or corrode.

Steamhead to be mounted 18" above floor or 6" above rim of tub and as far from the seating area as possible.

Rough-in Notes

Access: 21" L x 20" W x 22" H (28" L with Auto Drain)



STEMMIST® East Coast Office: 25 E. Union Ave., East Rutherford, NJ 07073 • Tel: 800-577-6478 • Fax: 201-933-0746

West Coast Office: Tel: 800-355-6478 • Fax: 661-940-1617