

Exposed Flush Valve for Urinals

Architectural/Engineering Specification:

Exposed, quiet diaphragm-type, chrome plated flushometer valve with a polished exterior. Complete with a chloramine resistant, dual seal diaphragm with a clog resistant by-pass. The valve is ADA compliant with a nonhold open and no leak handle feature. Internal seals are made of chloramine resistant materials.

Product Features:

- · Control Stop has internal siphon-guard protection, sweat solder kit, wall flange with set screw.
- · High back pressure vacuum breaker with one piece hex coupling nut
- · Chloramine resistant Internal seals
- Adjustable tailpiece
- · Spud coupling and flange for top spud connection

Valve Height Options:

Product No.	Α
Z6003	11 1/2" [292]
Z6003-1	16" [406]
Z6003-2	24" [610]
Z6003-3	27" [686]

Compliance and Certification:

ADA Compliant



*This product should be used with a WaterSense to ensure that the entire system meets the requirements for water efficiency and performance.



Flow Options:

	Flush Volume	WaterSense* Labeled
-ULF**	0.125 gpf	✓
-EWS**	0.5 gpf	✓
-WS1	1.0 gpf	

Suffix Options:

-BG	BioCare Handle
-L	1" [25] Metal Push Button
-VC	Vandal Resistant Stop Cover
-YB	Sweat Solder Kit
-YC	Cast Wall Flange
-YJ	Split Ring Pipe Support
-YK	Solid Ring Pipe Support

Upgrade Options:

Aquaflush Plus - includes Vandal Resistant Stop Cover and Proprietary Dezincification resistant low lead brass alloy body.

-TFB Triple Filter By-pass

** Not available w/-TFB

Architectural/Engineering Approval

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.



Rough-in/Overview dimensions

