

Type _____


-20 -126

P3902 ☐ ☐

P3903 ☐ ☐

P3904 ☐ ☐
Finish

Catalog No.	Antique Bronze	Burnished Silver	Lamping	Dimensions (Inches)		
				A	B	C
P3902	-20	-126	2 (c) 60w	10-7/8	17-1/8	92
P3903	-20	-126	3 (c) 60w	14	21-1/8	96
P3904	-20	-126	4 (c) 60w	18	26-3/4	104


Specifications:
General

- Square design with tapered bottom section
- Clear glass panels in roof and sides
- Matching candle covers and caps
- Antique Bronze (-20) and Burnished Silver (-126) are hand painted
- Steel construction
- Six feet of 9 gauge matching chain supplied
- P3902 and P3903 can be wall mounted with accessory arm P8762

Mounting

- Ceiling chain mounted
- Canopy covers a standard 4" recessed octagonal outlet box
 - P3902 canopy is 5-1/2" dia. x 1-1/2" ht.
 - P3903 and P3904 canopy is 7" dia. x 1-3/4" ht.
- Mounting strap for outlet box included

Electrical

- Phenolic candelabra based sockets
- 15 feet of wire
- Pre-wired

Labeling

- UL-CUL (P3902 and P3903) and cCSAus (P3904) listed