

CD Unipack 201™

The CD Unipack 201 is versatile, durable and includes an Alabaster light kit.



Brushed Nickel CD Unipack with 52" Contractor's Design
Rosewood Blades

Model-Finish **CDU201BN**
Blade-Finish **BCD52-DOK**
Light-Finish **Included**


Features

- Standard, 3 Speed Reversible Motor
- 2" and 4" Downrods *(Included)*
- 30 Year Limited Warranty
- Blades Sold Separately
- Alabaster Glass Bowl Kit (3-60W Candelabra Bulbs Included)**
- Universal Control Adaptable *(Optional)*
- Additional Blade Selections In 42" Size Available

Specs

- | | |
|--|------------|
| ■ Blade Sweep Opt. | 42", 52" |
| ■ Number of Blades | 5 |
| ■ Blade Pitch | 12° |
| ■ Motor Size (MM) | 153 x 12 |
| ■ AMPS (HI Speed) | 0.7 |
| ■ Watts (HI Speed) | 67 |
| ■ RPM (HI-MED-LOW) | 200-120-55 |
| ■ Shipping Wt. (lbs.) | 18 |
| ■ CU. FT. in Carton | 1.6 |
| ■ Airflow*
<i>(Cubic Feet Per Minute)</i> | 6,164 |
| ■ Electricity Use* | 67 Watts |
| ■ Airflow Efficiency*
<i>(Cubic Feet Per Minute Per Watt)</i> | 92 |

Ceiling Drop Dimensions



A: 2" DR - 15.0"	B: 2" DR - 8.5"
A: 4" DR - 17.5"	B: 4" DR - 10.0"
C: 11.0"	D: 5.125"
E: 3.5"	

DR: Downrod

Compare: 36" to 48" ceiling fans have airflow efficiencies ranging from approximately 71 to 86 cubic feet per minute per watt at high speed.

**Compare: 49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.*

** Due to 2005 EPACT regulations, light kits may be subject to change

Popular Combinations



White CD Unipack with 52" Contractor's Design White Blades

Model-Finish **CDU201W**
 Blade-Finish **BCD52-W**
 Light-Finish **Included**



Oiled Bronze CD Unipack with 52" Contractor's Design Oiled Bronze Blades

Model-Finish **CDU201OB**
 Blade-Finish **BCD52-OB**
 Light-Finish **Included**



Antique White CD Unipack with 52" Contractor's Design Antique White Blades

Model-Finish **CDU201AW**
 Blade-Finish **BCD52-AW**
 Light-Finish **Included**



Brownstone™† CD Unipack with 52" Contractor's Design Washed Walnut Birch Blades

Model-Finish **CDU201BS**
 Blade-Finish **BCD52-WWB**
 Light-Finish **Included**

Available Finishes



AB
Antique Brass



AW
Antique White




BN
Brushed Nickel



BS
Brownstone™†




EB
European Bronze




OB
Oiled Bronze



PB
Polished Brass



TW
Textured White



W
White

Blade Options

Type 5 Blades
(see page 200)



Light Kit Options

Bowl Light Kit Included

Remotes



Universal Remote Control System
(Optional)
 UC-2000 Series
(see page 223)

†Brownstone™ is a registered trademark of Dolan Designs