MOLF

OG30

FEATURES

Three individually contained grill burners for versatile cooking

Utilizes both direct and radiant heat for more thorough grilling

Two-position rotisserie handles foods big and small

Heavy-duty stainless steel construction

Rigorously tested in our U.S. manufacturing facilities for decades of use

Exceptional 24/7 support from our Customer Care team in Madison

Halogen lights for night-time grilling

Electric hot surface ignition for reliable start ups

Double-wall hood front holds in heat

Hood assist system makes opening and closing easy

Three-position warming rack for the exact temperature you want

Stainless steel burner grates

ACCESSORIES

Canvas covers

Stainless steel portable grill cart with fold-down side shelves

Stainless steel doors and drawers for built-in enclosure

Griddle Plate

Black control knob(s)

Accessories available through an authorized Sub-Zero dealer. For local dealer information, visit $\underline{\text{subzero-wolf.com/locator}}.$



KNOB OPTIONS





GRILL SPECIFICATIONS


- 1 25,000 Btu Burner
- 1 14,000 Btu Rotisserie Burner




PRODUCT SPECIFICATIONS

Model	OG30
Dimensions	30"W x 27"H x 30"D
Weight	216 lb
Electrical Supply	120 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Gas Supply	3/4" rigid pipe
Gas Inlet	1/2" NPT female
Power Cord Length	5 feet


ELECTRICAL AND GAS



DIMENSIONS



STANDARD INSTALLATION



FRONT VIEW

NOTE: Shaded area above countertop indicates minimum clearance to combustible surfaces, combustible materials cannot be located within this area.