

### Professional Custom Series Built-In Gas 30"/36"W.

# COOKING s Built-In Gas 30"/36"W. Sealed Burner Rangetop

### Standard Features & Accessories

#### All models include

- Exclusive VSH<sup>™</sup> Pro Sealed Burner System (VariSimmer<sup>™</sup> to High) combination of patented burner and top design provide ease of cleaning plus superior performance at simmer and high
- Exclusive VariSimmer setting for all burners
- Exclusive tooled and porcelainized cooking surface contains spills for easy cleaning
- Brass sealed burners with porcelain/cast iron caps and automatic ignition/re-ignition
- Durable knobs with childproof, push-to-turn safety feature

#### 30"W. 4B model includes

- Three 15,000 BTU burners
- One TruPower Plus<sup>™</sup> 18,500 BTU burner
- Center grate allows movement of cooking vessels across entire top surface

#### 36"W. 6B model includes

- Five 15,000 BTU burners
- One TruPower Plus™ 18,500 BTU burner

### 36"W. 4G model includes

- Four 15,000 BTU burners
- 12"W. thermostatically controlled steel griddle/simmer plate

#### 36"W. 4Q model includes

- Four 15,000 BTU burners
- 12"W. grill with flavor generator plates and automatic ignition/re-ignition

### **Model Options**





VGRT530-4B\* 30"W. Four-Burner Rangetop



VGRT536-6B\* 36"W. Six-Burner Rangetop



VGRT536-4G\* 36"W. Four-Burner/ Griddle Rangetop



VGRT536-4Q\* 36"W. Four-Burner/ Grill Rangetop

### FINISH DETAILS FOR ALL MODELS

- Stainless Steel (SS) and White (WH).
  - o Stainless units have black porcelain grates, black porcelain burner caps, black porcelain grate support and stainless knobs.
- White (WH)
  - White finishes have black porcelain grates, black porcelain burner caps, white porcelain grate support and white knobs.
- Brass Accent Option (BR)—nameplate and knob bezels. Brass components have a durable protective coating for maintenance-free normal use.

\*Shown throughout with island trim. See Installation Notes & Accessories for details.

### ORDERING INSTRUCTIONS

First specify model number, and then color code (VGRT530-4BSSBR). If ordering brass accent option, specify code at end (VGRT530-4BSSBR). If ordering optional LP conversion, specify code at end (VGRT530-4BSSBRLP).





### **COOKING**

# Professional Custom Series Built-In Gas 30"/36"W. Sealed Burner Rangetop



Please see
Installation Notes &
Accessories
for important
installation
information,
including island
trim, backguard,
and high-shelf.




Star-K Kosher Certification for use on the Jewish Sabbath or Jewish holidays


### **Dimensions & Specifications**


**PRODUCT DIMENSIONS** 



VGRT530-4B 30"W. Four-Burner Rangetop VGRT536-6B 36"W. Six-Burner Rangetop VGRT536-4G 36"W. Four-Burner/ Griddle Rangetop VGRT536-4Q 36"W. Four-Burner/ Grill Rangetop








	VGRT530	VGRT536
Overall width	29-7/8" (75.9 cm)	35-7/8" (91.1 cm)
Overall height (from bottom)		
To top of grate	9	7-1/4" (23.5 cm)
To top of island trim	9	7-1/8" (23.2 cm)
Additions to base height		
To top of backguard	A	dd 8" (20.3 cm)
To top of high shelf	Add	23-1/2" (72.9 cm)
Overall depth (from rear)		
To end of side panel	24	-5/16" (61.8 cm)
To end of landing ledge	28	-1/16" (71.3 cm)
To end of knobs	28	-9/16" (72.6 cm)

### **Dimensions & Specifications**

#### **CLEARANCE DIMENSIONS**



А		
30"W.	29-7/8" (75.9 cm)	
36"W.	35-7/8" (91.1 cm)	

### Minimum clearances from adjacent combustible construction

- Cooking surface and below, i.e., 36" (91.4 cm) and below
   Sides—0"
- o Sides—0"
  o Rear—0" with backguard or
  highshelf; 0" with island trim
  and non-combustible rear wall;
  6" (15.2 cm) with island trim and
  combustible rear wall.
- Above cooking surface, i.e. above 36" (91.4 cm)
  - o Sides—6" (15.2 cm)
  - o Within 6" (15.2 cm) side clearance, wall cabinets no deeper than 13" (33.0 cm) must be minimum 18" (45.7 cm) above cooking surface.
- o Wall cabinets directly above product must be minimum 42" (106.7 cm) above cooking surface.





### COOKING





### UTILITY REQUIREMENTS



#### GAS

- o Shipped natural or propane gas; field convertible with conversion kit.
- o Accepts standard residential 1/2" (1.3 cm) ID gas service line
- o Gas manifold pressure
- o Natural gas 5.0" W.C.P.
- o LP/Propane 10.0" W.C.P.



### **ELECTRICAL**

- Four-foot (121.9 cm) cord included with rangetop
- Three-wire with ground/three-prong plug
- 120 V/60 Hz
- Max. amp usage o 4B—0.5
- o 6B—0.5
- o 4G—0.5
- o 4Q-0.5




**PLUMBING**Not applicable

### **Installation Requirements**

### **ACCESS REQUIREMENTS**



VGRT530-4B 30"W. Four-Burner Rangetop VGRT536-6B 36"W. Six-Burner Rangetop VGRT536-4G 36"W. Four-Burner/ Griddle Rangetop VGRT536-4Q 36"W. Four-Burner/ Grill Rangetop



\*Note: 120 VAC/50Hz within 48" (121.9 cm) of right rear of rangetop

	VGRT530-4B	VGRT536-6B	VGRT536-4G	VGRT536-4Q
Cutout width	30" (76.2 cm)	36" (91.4 cm)	36" (91.4 cm)	36" (91.4 cm)
Cutout height	7-5/8" (19.4 cm)			
Cutout depth		24" (61.0 cm) min. to 25-3/	4" (65.4 cm) max.	
Surface burner rating				
TruPower Plus™ burner	18,500 BTU Nat. (5.4 kW)/	18,500 BTU Nat. (5.4 kW)/	15,000 BTU Nat. (4.4 kW)/	15,000 BTU Nat. (4.4 kW)/
(front right)	16,600 BTU LP (4.9 kW)	16,600 BTU LP (4.9 kW)	13,500 BTU LP (4.0 kW)	13,500 BTU LP (4.0 kW)
Other Burners	15,000 BTU Nat. (4.4 kW)/	15,000 BTU Nat. (4.4 kW)/	15,000 BTU Nat. (4.4 kW)/	15,000 BTU Nat. (4.4 kW)/
	13,500 BTU LP (4.0 kW)	13,500 BTU LP (4.0 kW)	13,500 BTU LP (4.0 kW)	13,500 BTU LP (4.0 kW)
Griddle			18,000 BTU Nat. (5.3 kW)/	15,000 BTU Nat. (4.4 kW)/
			16,000 BTU LP (4.7 kW)	12,500 BTU LP (3.7 kW)
Grill			18,000 BTU Nat. (5.3 kW)/	15,000 BTU Nat. (4.4 kW)/
			16,000 BTU LP (4.7 kW)	12,500 BTU LP (3.7 kW)



## Professional Custom Series Built-In Gas 30"/36"W. Sealed Burner Rangetop



COOKING

### Installation Notes & Accessories

A backguard, high-shelf, or island trim must be used for all installations.

#### **Island Trim**

- Stainless Steel (SS)
- Coordinates with all finishes
- For island/peninsula installation
- Included and shipped standard

Model	Description	Approx. ship wt. lbs. (kg)
P30TII	30"W. island trim	10 (4.5)
P36TII	36"W. island trim	11 (5.0)

### 8"H. Backguard

- Stainless Steel (SS)
- Coordinates with all finishes

Model	Description	Approx. ship wt. lbs. (kg)
P30BG8	30"W. backguard	14 (6.3)
P36BG8	36"W. backguard	17 (7.7)

### **High-shelf**

- Stainless Steel (SS)
- Coordinates with all finishes
- Shelf comes attached to a 24"H. backguard

Model	Description	Approx. ship wt. lbs. (kg)
B30HS24	30"W. high-shelf	45 (20.3)
B36HS24	36"W. high-shelf	50 (22.5)

### **Countertop Side Trim**

- Stainless Steel (SS)
- Coordinates with all finishes
- Installs on side of unit; overlaps countertop
- One pair of trim

Model	Description	Approx. ship wt. lbs. (kg)
P24CST	24"D. side trim	2 (0.9)

### **Countertop Rear Trim**

Stainless Steel (SS)

Model	Description	Approx. ship wt. lbs. (kg)
P30CRT	30"W. countertop rear trim	2 (0.9)
P36CRT	36"W counterton rear trim	2 (0.9)

### LP/Propane Conversion Kit

Allows for field conversion of range from natural gas to LP

Model	Description	Approx. ship wt. lbs. (kg)
LPKPDR	Natural to LP/propane conversion kit	2 (0.9)

### **Compliance Information**





### **WARRANTY INFORMATION\***

- Three-year full warranty—complete product
- Five-year limited warranty—surface burners, griddle burners and grill burners
- Ninety-day limited warranty—cosmetic parts such as glass, painted, and decorative items

<sup>\*</sup> For complete warranty see Use & Care Guide. Warranty valid on Viking products shipped within the United States and Canada.

