### **Grounding Fittings**

## **Grounding Rod Clamps - Direct Burial Type**



For terminating bare copper conductor to ground rod. Conductor range #10 solid to #2 stranded.

(I) File No. E20412

Clamps meet both UL and NEC requirements for burial in earth or embedment in concrete.

#### **Bronze**

Catalog Number	Ground Pipe Grounding Electrode Size	Unit Qty.	Std. Pkg. Qty.
GRC-50	1/2"	100	400
GRC-63	5/8"	50	200
GRC-75	3/4"	50	200

# Rebar Ground Clamps - Direct Burial Type





**RB-16** 

**RB-17** 

For making connection with #10 AWG solid to #2 AWG stranded copper wire to 1/2" to 1" ground water pipe or 3/8" to 1" rebar. All materials contain minimum of 80% copper.

(II) File No. E20412

Clamps meet both UL and NEC requirements for burial in earth or embedment in concrete.

#### **Bronze**

Catalog	Ground	Rebar	Unit	Std. Pkg.
Number	Pipe		Qty.	Qty.
RB-16	1/2" - 1"	3/8" - 1"	20	200
RB-17	1/2" - 1"	3/8" - 1"	20	200

