

30" Gas Freestanding Range

300 Series – Stainless Steel HGS3053UC



HGS3053UC
Stainless Steel

Also available in:

White HGS3023UC
Black HGS3063UC

Five burner gas ranges offer the maximum burner performance and ultimate cooking flexibility.

Features & Benefits

PowerBoil provides quick heating with powerful 16,000 BTU.

Continuous grates are easy to clean and let you effortlessly move pots and pans.

500 BTU simmer burner easily heats delicate sauces without scorching or burning.

Self clean cycle quickly and easily cleans your oven to save you time.

Sealed burners provide excellent cleanability in case of spills.

General Properties

Oven Capacity	5.0 cu. ft.
Cooking modes	Bake and Broil
Cleaning type	Self Clean
Type of grate	Cast iron
Knob material	Plastic
Drawer type	Storage drawer
Sealed burners	Yes

Oven Performance

Bake burner power	18,000 BTU
Broil burner power	13,500 BTU

Burner Performance

Total number of cooktop burners	5
Total cooktop (NG) BTU	52,000 BTU
Power of front left burner (NG) BTU	9,500 BTU
Power of back left burner (NG) BTU	12,000 BTU
Power of center burner (NG) BTU	9,500 BTU
Power of back right burner (NG) BTU	5,000 BTU
Power of front right burner (NG) BTU	16,000 BTU



Technical Details

Watts (W)	1,800 W
Circuit breaker (A)	15 A
Volts (V)	120 V
Frequency (Hz)	60 Hz
Plug type	120V-3 prong
Cord Length	46"
Energy source	Gas
Gas type	Natural gas 15 mbar (USA)
Alternative gas type	LP 27, 5 mbar (USA)

Dimensions & Weight

Overall appliance dimensions (HxWxD)(in.)	47 3/4" x 29 7/8" x 25 3/4"
Required cutout size (HxWxD) (in.)	30" width freestanding
Adjustable range height (in.)	3/4"
Net weight (lbs)	204

Accessories—Included

Included	Oven racks x 2
----------	----------------

Accessories—Optional

LP kit	HEZ1090
--------	---------

For help and assistance with Bosch accessories please visit: www.bosch-eshop.com/eshop/bosch/us or call 1-800-944-2904 Mon-Fri 5am to 6pm PST Sat 6am to 3pm PST

Notes: All height, width and depth dimensions are shown in inches. Please refer to installation instructions prior to making cutout. BSH reserves the absolute and unrestricted right to change product materials and specifications, at any time, without notice. Consult the product's installation instructions for final dimensional data and other details. Applicable product warranty can be found in accompanying product literature or you may contact your account manager for further details.

Warranties: Bosch warrants that the Product is free from defects in materials and workmanship for a period of three hundred and sixty-five (365) days from the date of purchase. The foregoing timeline begins to run upon the date of purchase, and shall not be stalled, tolled, extended, or suspended, for any reason whatsoever. This Product is also warranted to be free from cosmetic defects in material and workmanship (such as scratches of stainless steel, paint/porcelain blemishes, chip, dents, or other damage to the finish of the Product, for a period of thirty (30) days from the date of purchase or closing date for new construction. This cosmetic warranty excludes slight color variations due to inherent differences in painted and porcelain parts, as well as differences caused by kitchen lighting, product location, or other similar factors. This cosmetic warranty specifically excludes any display, floor, "As Is", or "B" stock appliances.

For more information on our entire line of products, go to www.bosch-home.com/us or call 1-800-944-2904


© BSH Home Appliances Corporation. All rights reserved. Bosch is a registered trademark of Robert Bosch GmbH.

30" Gas Freestanding Range

300 Series – Stainless Steel HGS3053UC



Installation Details



Dimensions in inches

For help and assistance with Bosch accessories please visit: www.bosch-eshop.com/eshop/bosch/us or call 1-800-944-2904 Mon-Fri 5am to 6pm PST Sat 6am to 3pm PST

Notes: All height, width and depth dimensions are shown in inches. Please refer to installation instructions prior to making cutout. BSH reserves the absolute and unrestricted right to change product materials and specifications, at any time, without notice. Consult the product's installation instructions for final dimensional data and other details. Applicable product warranty can be found in accompanying product literature or you may contact your account manager for further details.

Warranties: Bosch warrants that the Product is free from defects in materials and workmanship for a period of three hundred and sixty-five (365) days from the date of purchase. The foregoing timeline begins to run upon the date of purchase, and shall not be stalled, tolled, extended, or suspended, for any reason whatsoever. This Product is also warranted to be free from cosmetic defects in material and workmanship (such as scratches of stainless steel, paint/porcelain blemishes, chip, dents, or other damage to the finish of the Product, for a period of thirty (30) days from the date of purchase or closing date for new construction. This cosmetic warranty excludes slight color variations due to inherent differences in painted and porcelain parts, as well as differences caused by kitchen lighting, product location, or other similar factors. This cosmetic warranty specifically excludes any display, floor, "As Is", or "B" stock appliances.

For more information on our entire line of products, go to www.bosch-home.com/us or call 1-800-944-2904

© BSH Home Appliances Corporation. All rights reserved. Bosch is a registered trademark of Robert Bosch GmbH.