




BP220**1/BP225OB1 Series Ceiling Fans



Net Hanging Weight: 18.5 lbs

	A	B
Fan In Close to Ceiling Configuration	15.48"	7.74"

	A	B
Fan w/4.5" downrod	19.30"	11.10"
Fan w/12" downrod	26.80"	18.60"
Fan w/18" downrod	32.80"	24.60"
Fan w/24" downrod	38.80"	30.60"
Fan w/36" downrod	50.80"	42.60"
Fan w/48" downrod	62.80"	54.60"
Fan w/60" downrod	74.80"	66.60"
Fan w/72" downrod	86.80"	78.60"

Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	188	5897	92	0.53	64
Med	124	3701	128	0.37	29
Low	65	1744	174	0.21	10

INSTALLATION REQUIREMENTS:

Fan must be attached to a securely anchored electrical junction box capable of withstanding a load of at least 50 lbs.

ELECTRICAL REQUIREMENTS:

Requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

MOTOR SPECS:

153 x 15 motor is designed for optimal performance with this fan.

BLADES:

A set of five 20.7" traditional wood blades is included.

CONTROL OPTIONS:

Optional CW1, CW1SW, CW2, CW5 and CWRL4 wall controls and CRL4WH and CRL8TS remote controls (with receiver units) are available—sold separately. Instructions are provided with each control.

LIGHTING OPTIONS:

A 3-bulb (60 watt max candelabra bulbs - included) downlight fixture with 1 bowl glass shades is included with this fan assembly. Maximum downlight wattage not to exceed 180 watts.

DOWNROD OPTIONS:

Dual mount for flush mount application or 1" dia x 4.5" long downrod. Optional downrods available in 12", 18", 24", 36", 48", 60", and 72" lengths. A downrod coupler is available for installations requiring a downrod longer than 72". Fan can be mounted on a sloped ceiling up to 30°. Most sloped ceiling installations require a downrod longer than the standard 6" downrod. Call technical support for more information.

LOCATION USE:

Fans are rated for dry locations only.

Available Finishes—BP220**	
Fan Assembly / Glass	Blades - Traditional
MW – Matte white / Frosted White	Matte white
OB – Oil-rubbed bronze / Amber	Cherry / walnut reversible
SN – Satin nickel / Frosted white	Cherry / walnut reversible

Available Finishes—BP225OB	
Fan Assembly / Glass	Blades - Traditional
OB – Oil-rubbed bronze / Frosted White	Cherry / walnut reversible