MultiChoice® Universal Thermostatic Tub and Sh		<b>O</b> ELTA	
<ul> <li>Concealed in-wall MultiChoice<sup>®</sup> Universal valve</li> <li>Back-to-back capability, Integral screwdriver stops</li> <li>Heavy duty forged brass valve body</li> <li>1/2<sup>®</sup> Universal inlets to accept 1/2<sup>®</sup> copper,</li> </ul>	<ul> <li>T17TH FINISH TRIM ONLY:</li> <li>TempAssure® 17T Thermostatic cartridge</li> <li>Polished chrome-plated finish</li> <li>ADA compliant handle</li> <li>Lever volume control; temperature adjustment dial</li> <li>Non-removeable red/blue temperature markings and with (add product variation)</li> </ul>	T17TH155	
Requires rough-in and trim to have complete product.	with (add shower)	Engineer/Architect Appro Model Specified: Approval:	Date:
MODEL NUMBER EXAMPLE: Configurations vary, see below for availability.       T17TH1555-25         Variation 1 = Shower valve 2 = Tub & shower valve with pull-up diverter tub spout* 3 = Shower valve with diverter for dual showers. See DSP-T17TH3.       Shower 0 = No shower head 2 = 3-function Touch-Clean* shower head/arm/flange 5 = Hand shower with 24" SS grab bar and ADA slide       Handle 5 = Metal lever volume control with temperature adjustment			
AVAILABLE MODELS	1 Shower Valve ONLY	VARIATION 2 Tub and Shower*	acing 24" bar and vinyl hose
	HANDLE 5 Vandal Resistant Metal Lever Volume Control	5 Vandal Resistant Metal Lever Volume Control	HANDLE
O No Shower Head (Note 1)	T17TH105	T17TH205	~
2 3-Function Touch-Clean® Shower Head, Arm, Flange 1.75 gpm (6.6 L/min)	T17TH125		
3 Touch-Clean* Shower Head, Arm, Flange 1.75 gpm (6.6 L/min)	T17TH135		
5 Hand Shower with 2 Check Valves, 24" (610 mm) SS Bar with ADA Slide 2.5 gpm (9.5 L/min)	T17TH155 T17TH155-05 T17TH155-20 T17TH155-25		

## See DSP-B-R10000-HDF for additional rough-in options. See DSP-SHWA and DSP-SHWB for additional shower options. Note 1: Valve rated minimum 1.7 gpm @ 45 psi (6.4 L/min @ 310 kPa). \*Tub spout diverter not ADA

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.

Note: Use this page front and back as a product submittal sheet. Refer to www.specselect.com for individual models. Stated flow rate for shower heads @ 80 psi (552 kPa) maximum.

## MultiChoice<sup>®</sup> Universal Thermostatic Tub and Shower





## **APPROVALS:**


- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- Lindicates compliance to ICC/ANSI A117.1
- Tub spout diverter NOT ADA
- Thermostatic Valve complies with ASSE 1016
- Hand Shower back flow protection provided by two integral certified check valves in series, which operate independently, ASME A112.18.3

(Contact Delta Representative for State and/or Local Approvals.)










Note: Measurements may vary ± 6mm (0.25")

Note: Use this page front and back as a product submittal sheet.

Refer to www.specselect.com for individual models.



Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.