

THE I-20 IS THE ROTOR THAT'S GOT ALL THE FEATURES YOU NEED.

FEATURES

- Models: Shrub, 4", 6", 12"
- Models (stainless riser): 4", 6"
- Arc setting: 50 to 360 degrees
- Nozzle choices: 22
- Nozzle racks: 1.5 to 8.0 blue, 2.0 LA to 4.5 LA gray, 0.50 to 3.0 black, 6.0 to 13.0 green
- Factory installed rubber cover
- Through-the-top arc adjustment
- Quick check arc mechanism
- Water lubricated gear-drive
- Warranty period: 5 years

ADVANCED FEATURES

- Automatic arc return
- Non-strippable drive
- Part- and full-circle in one model
- Headed and slotted set screw
- FloStop® control
- Reclaimed water ID (optional)
- Stainless steel riser (optional)
- Drain check valve (up to 10' of elevation)
- Low angle nozzle choices

OPERATING SPECIFICATIONS

Radius: 17' to 46'

Flow Rate: 0.36 to 14.8 GPM

Recommended pressure range:
30 to 70 PSI

Operating pressure range: 20 to 100 PSI

Precipitation rates: 0.4 in/hr approx.

Nozzle trajectory: Std = 25 degrees,
Low angle = 13 degrees

FACTORY INSTALLED OPTIONS

Nozzles: 1.5 to 4.0

Reclaimed water ID cover



I-20-00: Overall height: 7¾"
Exposed diameter: 1¾"
Inlet size: ¾" female NPT



I-20-04: Overall height: 7⅞"
Pop-up height: 4"
Exposed diameter: 1¾"
Inlet size: ¾" female NPT



I-20-06: Overall height: 9⅞"
Pop-up height: 6"
Exposed diameter: 1¾"
Inlet size: ¾" female NPT



I-20-12: Overall height: 17"
Pop-up height: 12"
Exposed diameter: 1¾"
Inlet size: ¾" female NPT



SPECIFICATIONBUILDER

www.hunterindustries.com/I20

MODELS	STANDARD FEATURES	FEATURE OPTIONS		NOZZLE OPTIONS
I-20-00 = Shrub	Adjustable arc, plastic riser, check valve, 8 standard nozzles, and 4 low-angle nozzles	R	NCV = Without check valve R = Reclaimed water ID	1.5 to 4.0 = Factory installed nozzle number
I-20-04 = 4" pop-up		NCV, R		
I-20-06 = 6" pop-up		R		
I-20-12 = 12" pop-up		R		

MODELS	STANDARD FEATURES	FEATURE OPTIONS		NOZZLE OPTIONS
I-20-04-SS = 4" pop-up	Adjustable arc, stainless steel riser, check valve 8 standard nozzles, and 4 low-angle nozzles	NCV, R	NCV = Without check valve R = Reclaimed water ID	1.5 to 4.0 = Factory installed nozzle number
I-20-06-SS = 6" pop-up		R		

EXAMPLES

I-20-04	4" pop-up, adjustable arc
I-20-12 - NCV - R - 4.0	12" pop-up, adjustable arc, without check valve, with reclaimed water ID, and 4.0 nozzle
I-20-06-SS - R - 3.0	6" pop-up, adjustable arc, stainless steel, reclaimed water ID, and 3.0 nozzle