

Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Double (equal) bowl.
- Top-mount.
- Two faucet holes.
- 33" (838 mm) x 22" (559 mm)

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

- K- 6016L Sink Rack K- 6016R Sink Rack K- 6545 Sponge Caddy K- 6603L Sink Basket K- 6603R Sink Basket
- K- 8801 Sink Strainer

Components

Product includes: 1054375 Under-mount Sink Kit, 23"



Codes/Standards ASME A112.19.1/CSA B45.2

KOHLER[®] Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
\bigcirc	0	White
\bigcirc	FF	Sea Salt™
\bigcirc	96	Biscuit
\bigcirc	47	Almond
\bigcirc	FD	Cane Sugar™
	95	Ice™ Grey


- G9 Sandbar
- K4 Cashmere
 - 20 Suede
 - KA Black 'n Tan
 - 7 Black Black™



Hartland[®] Top-mount Kitchen Sink K-5818-2



Hartland[®] Top-mount Kitchen Sink K-5818-2



Technical Information

All product dimensions are nominal.			
Bowl configuration:	Double equal		
Installation:	Top-mount		
Bowl area (Left)	Length: 14-1/8" (359 mm)		
	Width: 16-1/4" (413 mm)		
	Bowl depth: 9" (229 mm)		
Bowl area (Right)	Length: 14-1/8" (359 mm)		
	Width: 16-1/4" (413 mm)		
	Bowl depth: 9" (229 mm)		
Number of deck holes:	2		
Faucet hole(s):	1-3/8" (35 mm)		
Drain hole:	3-7/8" (98 mm)		
Template:	Top-mount, 1125670-7, required, included		

Notes

Install this product according to the installation guide.

NOTICE: The countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by the Kohler Co. (Call 1-800-4-KOHLER.) Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.

