



PROSELECT™

Product Specifications

240 VOLT WATER HEATER TUNE UP KITS




Fig. 1




Fig. 2

Fig. 3

TUNE UP KITS (includes 2 elements and Upper & lower t-stats)

PROSELECT PN	# OF ELEMENTS	VOLTAGE	WATTS @ 240	WATTS @ 208	WATT DENSITY	"A" DIA.	THREAD NPSM	MINIMUM TANK DIA.	PIC FOR FIGURE	THERMOSTATS
PSW12901	2	240	4500	3380	HIGH	12"	1"	13"	Fig. 1	UPPER & LOWER APCOM STYLE
PSW12902	2	240	4500	3380	HIGH	12"	1"	13"	Fig. 3	UPPER & LOWER TOD STYLE

A dimension is measured from flange to end of element

ADAPTORS

PROSELECT PN	OLD PROSELECT PN	FEATURES	PIC FOR FIGURE	ADDITIONAL FEATURES
PSW12317	PF9000030PK	Adapter kit for installing screw-in flanged elements to four bolt flanged element openings.	Fig. 2	Includes gaskets, hardware, bracket, & install instructions

Warranty and Codes

These PROSELECT products carry a 1-year limited warranty.